

Double ESD protection diodes for transient overvoltage suppression

Rev. 01 — 1 September 2008

**Product data sheet** 

#### **Product profile** 1.

### 1.1 General description

Unidirectional double ElectroStatic Discharge (ESD) protection diodes in a common anode configuration, encapsulated in a SOT23 (TO-236AB) small Surface-Mounted Device (SMD) plastic package. The devices are designed for ESD and transient overvoltage protection of up to two signal lines.

#### Table 1. **Product overview**

Type number <sup>[1]</sup>	Package		Configuration
	NXP	JEDEC	
MMBZ12VAL	SOT23	TO-236AB	dual common anode
MMBZ15VAL			
MMBZ18VAL			
MMBZ20VAL			
MMBZ27VAL			
MMBZ33VAL			

[1] All types available as /DG halogen-free version.

### **1.2 Features**

- Unidirectional ESD protection of two lines
- Bidirectional ESD protection of one line IEC 61000-4-2; level 4 (ESD)
- Low diode capacitance: C<sub>d</sub> ≤ 140 pF
- **Rated peak pulse power:**  $P_{PPM} \le 40 \text{ W}$
- Ultra low leakage current: I<sub>RM</sub> ≤ 5 nA

### 1.3 Applications

- Computers and peripherals
- Audio and video equipment
- Cellular handsets and accessories

- ESD protection up to 30 kV (contact) discharge)
- IEC 61643-321
- AEC-Q101 qualified
- Automotive electronic control units
- Portable electronics



### 1.4 Quick reference data

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
Per diode	)					
V <sub>RWM</sub>	reverse standoff voltage					
	MMBZ12VAL MMBZ12VAL/DG		-	-	8.5	V
	MMBZ15VAL MMBZ15VAL/DG		-	-	12	V
	MMBZ18VAL MMBZ18VAL/DG		-	-	14.5	V
	MMBZ20VAL MMBZ20VAL/DG		-	-	17	V
	MMBZ27VAL MMBZ27VAL/DG		-	-	22	V
	MMBZ33VAL MMBZ33VAL/DG		-	-	26	V
C <sub>d</sub>	diode capacitance	$f = 1 MHz; V_R = 0 V$				
	MMBZ12VAL MMBZ12VAL/DG		-	110	140	pF
	MMBZ15VAL MMBZ15VAL/DG		-	85	105	pF
	MMBZ18VAL MMBZ18VAL/DG		-	70	90	pF
	MMBZ20VAL MMBZ20VAL/DG		-	65	80	pF
	MMBZ27VAL MMBZ27VAL/DG		-	48	60	pF
	MMBZ33VAL MMBZ33VAL/DG		-	45	55	pF

## 2. Pinning information

Table 3.	Pinning		
Pin	Description	Simplified outline	Graphic symbol
1	cathode (diode 1)		_
2	cathode (diode 2)		3
3	common anode		

## 3. Ordering information

Table 4. Orderin	g informat	ion				
Type number	Package	Package				
	Name	Description	Version			
MMBZ12VAL	-	plastic surface-mounted package; 3 leads	SOT23			
MMBZ15VAL						
MMBZ18VAL						
MMBZ20VAL						
MMBZ27VAL						
MMBZ33VAL						
MMBZ12VAL/DG	-	plastic surface-mounted package; 3 leads	SOT23			
MMBZ15VAL/DG						
MMBZ18VAL/DG						
MMBZ20VAL/DG						
MMBZ27VAL/DG						
MMBZ33VAL/DG						

## 4. Marking

Type number	Marking code <sup>[1]</sup>	Type number	Marking code <sup>[1]</sup>
MMBZ12VAL	*H1	MMBZ12VAL/DG	TH*
MMBZ15VAL	*H2	MMBZ15VAL/DG	TK*
MMBZ18VAL	*H3	MMBZ18VAL/DG	TM*
MMBZ20VAL	*H4	MMBZ20VAL/DG	TP*
MMBZ27VAL	*H5	MMBZ27VAL/DG	TR*
MMBZ33VAL	*H6	MMBZ33VAL/DG	TT*

[1] \* = -: made in Hong Kong

\* = p: made in Hong Kong

\* = t: made in Malaysia

\* = W: made in China

#### Double ESD protection diodes for transient overvoltage suppression

## 5. Limiting values

Symbol	Parameter	Conditions	Min	Max	Unit
Per diode					
P <sub>PPM</sub>	rated peak pulse power	$t_p = 10/1000 \ \mu s$	[1][2] _	40	W
I <sub>PPM</sub>	rated peak pulse current	t <sub>p</sub> = 10/1000 μs	<u>[1][2]</u>		
	MMBZ12VAL MMBZ12VAL/DG		-	2.35	A
	MMBZ15VAL MMBZ15VAL/DG		-	1.9	A
	MMBZ18VAL MMBZ18VAL/DG		-	1.6	А
	MMBZ20VAL MMBZ20VAL/DG		-	1.4	A
	MMBZ27VAL MMBZ27VAL/DG		-	1	A
	MMBZ33VAL MMBZ33VAL/DG		-	0.87	A
Per device	)				
P <sub>tot</sub>	total power dissipation	$T_{amb} \le 25 \ ^{\circ}C$	[3] _	265	mW
			[4] _	360	mW
Tj	junction temperature		-	150	°C
T <sub>amb</sub>	ambient temperature		-55	+150	°C
T <sub>stg</sub>	storage temperature		-65	+150	°C

[1] In accordance with IEC 61643-321 (10/1000  $\mu s$  current waveform).

[2] Measured from pin 1 or 2 to pin 3.

[3] Device mounted on an FR4 Printed-Circuit Board (PCB), single-sided copper, tin-plated and standard footprint.

[4] Device mounted on an FR4 PCB, single-sided copper, tin-plated, mounting pad for cathode 1 cm<sup>2</sup>.

#### Table 7.ESD maximum ratings

T<sub>amb</sub> = 25 °C unless otherwise specified.

Symbol	Parameter	Conditions		Min	Мах	Unit
Per diode						
V <sub>ESD</sub>	electrostatic discharge voltage		[1][2]			
		IEC 61000-4-2 (contact discharge)		-	30	kV
		machine model		-	2	kV


[1] Device stressed with ten non-repetitive ESD pulses.

[2] Measured from pin 1 or 2 to pin 3.

#### Double ESD protection diodes for transient overvoltage suppression



Standard	Conditions
Per diode	
IEC 61000-4-2; level 4 (ESD)	> 15 kV (air); > 8 kV (contact)
MIL-STD-883; class 3 (human body model)	> 8 kV



## 6. Thermal characteristics

#### Table 9.Thermal characteristics

Symbol	Parameter	Conditions	Mi	in	Тур	Max	Unit
Per device	e						
R <sub>th(j-a)</sub>	thermal resistance from junction to ambient	in free air	<u>[1]</u> -		-	460	K/W
			[2] _		-	340	K/W
R <sub>th(j-sp)</sub>	thermal resistance from junction to solder point		<u>[3]</u> _		-	50	K/W

[1] Device mounted on an FR4 PCB, single-sided copper, tin-plated and standard footprint.

[2] Device mounted on an FR4 PCB, single-sided copper, tin-plated, mounting pad for cathode 1 cm<sup>2</sup>.

[3] Measured from pin 1 or 2 to pin 3.

MMBZXVAL SER 1

Double ESD protection diodes for transient overvoltage suppression

## 7. Characteristics

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
Per diod	e					
VF	forward voltage	I <sub>F</sub> = 10 mA	-	-	0.9	V
V <sub>RWM</sub>	reverse standoff voltage					
	MMBZ12VAL MMBZ12VAL/DG		-	-	8.5	V
	MMBZ15VAL MMBZ15VAL/DG		-	-	12	V
	MMBZ18VAL MMBZ18VAL/DG		-	-	14.5	V
	MMBZ20VAL MMBZ20VAL/DG		-	-	17	V
	MMBZ27VAL MMBZ27VAL/DG		-	-	22	V
	MMBZ33VAL MMBZ33VAL/DG		-	-	26	V
I <sub>RM</sub>	reverse leakage currer	ıt				
	MMBZ12VAL MMBZ12VAL/DG	V <sub>RWM</sub> = 8.5 V	-	0.1	5	nA
	MMBZ15VAL MMBZ15VAL/DG	V <sub>RWM</sub> = 12 V	-	0.1	5	nA
	MMBZ18VAL MMBZ18VAL/DG	V <sub>RWM</sub> = 14.5 V	-	0.1	5	nA
	MMBZ20VAL MMBZ20VAL/DG	V <sub>RWM</sub> = 17 V	-	0.1	5	nA
	MMBZ27VAL MMBZ27VAL/DG	$V_{RWM} = 22 V$	-	0.1	5	nA
	MMBZ33VAL MMBZ33VAL/DG	V <sub>RWM</sub> = 26 V	-	0.1	5	nA
V <sub>BR</sub>	breakdown voltage	I <sub>R</sub> = 1 mA				
	MMBZ12VAL MMBZ12VAL/DG		11.4	12	12.6	V
	MMBZ15VAL MMBZ15VAL/DG		14.25	15	15.75	V
	MMBZ18VAL MMBZ18VAL/DG		17.1	18	18.9	V
	MMBZ20VAL MMBZ20VAL/DG		19	20	21	V
	MMBZ27VAL MMBZ27VAL/DG		25.65	27	28.35	V
	MMBZ33VAL MMBZ33VAL/DG		31.35	33	34.65	V

#### Double ESD protection diodes for transient overvoltage suppression

Symbol	Parameter	Conditions		Min	Тур	Max	Unit
C <sub>d</sub>	diode capacitance	$f = 1 MHz; V_R = 0 V$					
	MMBZ12VAL MMBZ12VAL/DG			-	110	140	pF
	MMBZ15VAL MMBZ15VAL/DG			-	85	105	pF
	MMBZ18VAL MMBZ18VAL/DG			-	70	90	pF
	MMBZ20VAL MMBZ20VAL/DG			-	65	80	pF
	MMBZ27VAL MMBZ27VAL/DG			-	48	60	pF
	MMBZ33VAL MMBZ33VAL/DG			-	45	55	pF
V <sub>CL</sub>	clamping voltage		[1][2]				
	MMBZ12VAL MMBZ12VAL/DG	I <sub>PPM</sub> = 2.35 A		-	-	17	V
	MMBZ15VAL MMBZ15VAL/DG	I <sub>PPM</sub> = 1.9 A		-	-	21	V
	MMBZ18VAL MMBZ18VAL/DG	I <sub>PPM</sub> = 1.6 A		-	-	25	V
	MMBZ20VAL MMBZ20VAL/DG	I <sub>PPM</sub> = 1.4 A		-	-	28	V
	MMBZ27VAL MMBZ27VAL/DG	$I_{PPM} = 1 A$		-	-	40	V
	MMBZ33VAL MMBZ33VAL/DG	I <sub>PPM</sub> = 0.87 A		-	-	46	V
Sz	temperature coefficient	$I_Z = 1 \text{ mA}$					
	MMBZ12VAL MMBZ12VAL/DG			-	8.2	-	mV/K
	MMBZ15VAL MMBZ15VAL/DG			-	11	-	mV/k
	MMBZ18VAL MMBZ18VAL/DG			-	14	-	mV/k
	MMBZ20VAL MMBZ20VAL/DG			-	15.8	-	mV/k
	MMBZ27VAL MMBZ27VAL/DG			-	23	-	mV/k
	MMBZ33VAL			-	29.8	-	mV/k

### Table 10. Characteristics ...continued

[1] In accordance with IEC 61643-321(10/1000  $\mu$ s current waveform).


[2] Measured from pin 1 or 2 to pin 3.

MMBZ33VAL/DG

### **NXP Semiconductors**


## **MMBZxVAL** series

#### Double ESD protection diodes for transient overvoltage suppression




MMBZXVAL SER 1

Double ESD protection diodes for transient overvoltage suppression



## 8. Application information

The MMBZxVAL series is designed for the protection of up to two unidirectional data or signal lines from the damage caused by ESD and surge pulses. The devices may be used on lines where the signal polarities are either positive or negative with respect to ground. The devices provide a surge capability of 40 W per line for a 10/1000  $\mu$ s waveform.



#### Double ESD protection diodes for transient overvoltage suppression

#### Circuit board layout and protection device placement

Circuit board layout is critical for the suppression of ESD, Electrical Fast Transient (EFT) and surge transients. The following guidelines are recommended:


- 1. Place the devices as close to the input terminal or connector as possible.
- 2. The path length between the device and the protected line should be minimized.
- 3. Keep parallel signal paths to a minimum.
- 4. Avoid running protected conductors in parallel with unprotected conductors.
- 5. Minimize all Printed-Circuit Board (PCB) conductive loops including power and ground loops.
- 6. Minimize the length of the transient return path to ground.
- 7. Avoid using shared transient return paths to a common ground point.
- 8. Ground planes should be used whenever possible. For multilayer PCBs, use ground vias.

## 9. Test information

#### 9.1 Quality information

This product has been qualified in accordance with the Automotive Electronics Council (AEC) standard *Q101* - *Stress test qualification for discrete semiconductors*, and is suitable for use in automotive applications.

### **10. Package outline**



MMBZXVAL SER 1

## **11. Packing information**


#### Table 11. Packing methods

Type number	Package	Description	Packing	Packing quantity		
			3000	10000		
MMBZ12VAL	SOT23	4 mm pitch, 8 mm tape and reel	-215	-235		
MMBZ15VAL						
MMBZ18VAL						
MMBZ20VAL						
MMBZ27VAL						
MMBZ33VAL						
MMBZ12VAL/DG	SOT23	4 mm pitch, 8 mm tape and reel	-215	-235		
MMBZ15VAL/DG						
MMBZ18VAL/DG						
MMBZ20VAL/DG						
MMBZ27VAL/DG						
MMBZ33VAL/DG						

[1] For further information and the availability of packing methods, see Section 15.

Double ESD protection diodes for transient overvoltage suppression

## 12. Soldering



Double ESD protection diodes for transient overvoltage suppression

## 13. Revision history

Table 12. Revision history					
Document ID	Release date	Data sheet status	Change notice	Supersedes	
MMBZXVAL_SER_1	20080901	Product data sheet	-	-	

## 14. Legal information

### 14.1 Data sheet status

Document status[1][2]	Product status <sup>[3]</sup>	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

[1] Please consult the most recently issued document before initiating or completing a design.

[2] The term 'short data sheet' is explained in section "Definitions".

[3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL http://www.nxp.com.

### 14.2 Definitions

**Draft** — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local NXP Semiconductors sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

### 14.3 Disclaimers

**General** — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information.

**Right to make changes** — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in medical, military, aircraft, space or life support equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors accepts no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk. **Applications** — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) may cause permanent damage to the device. Limiting values are stress ratings only and operation of the device at these or any other conditions above those given in the Characteristics sections of this document is not implied. Exposure to limiting values for extended periods may affect device reliability.

Terms and conditions of sale — NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at <a href="http://www.nxp.com/profile/terms">http://www.nxp.com/profile/terms</a>, including those pertaining to warranty, intellectual property rights infringement and limitation of liability, unless explicitly otherwise agreed to in writing by NXP Semiconductors. In case of any inconsistency or conflict between information in this document and such terms and conditions, the latter will prevail.

**No offer to sell or license** — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

**Quick reference data** — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

**ESD protection devices** — These products are only intended for protection against ElectroStatic Discharge (ESD) pulses and are not intended for any other usage including, without limitation, voltage regulation applications. NXP Semiconductors accepts no liability for use in such applications and therefore such use is at the customer's own risk.

#### 14.4 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

## **15. Contact information**

For more information, please visit: http://www.nxp.com

For sales office addresses, please send an email to: salesaddresses@nxp.com

### **NXP Semiconductors**

## **MMBZxVAL** series

Double ESD protection diodes for transient overvoltage suppression


### 16. Contents

Product profile 1
General description
Features
Applications 1
Quick reference data
Pinning information 2
Ordering information 3
Marking 3
Limiting values 4
Thermal characteristics 5
Characteristics 6
Application information 9
Test information 10
Quality information 10
Package outline 10
Packing information
Soldering 12
Revision history 13
Legal information 14
Data sheet status 14
Definitions 14
Disclaimers
Trademarks 14
Contact information 14
Contents 15

Please be aware that important notices concerning this document and the product(s) described herein, have been included in section 'Legal information'.

#### © NXP B.V. 2008.

All rights reserved.



Date of release: 1 September 2008 Document identifier: MMBZXVAL\_SER\_1

