Disclaimer. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications



socket RPZ - mixed contact - 16 A - < 250 V - screw clamp - for relay RPM4

RPZF4

Main

Range of product	Harmony Electromechanical Relays
Device short name	RPZ
Product or component type	Socket
Product compatibility	Plug-in relay RPM with 4 C/O contact
Contacts type and composition	4 C/O
[Ith] conventional free air thermal current	16 A
[Ue] rated operational voltage	< 250 V

Complementary

Shape of pin	Flat
Contact terminal arrangement	Mixed
Tightening torque	< 1 N.m for M3.5 screw(s)
Fixing mode	By screw (panel) Clip-on (35 mm symmetrical DIN rail)
[Uimp] rated impulse withstand voltage	4 kV
overvoltage category	III
pollution degree	3
Sale per indivisible quantity	10
Width	50 mm
Product weight	0.094 kg

Environment

Connections - terminals	 screw clamp terminals, flexible cable with cable end 1 x 0.51 x 2.5 mm² / AWG 20AWG 14 screw clamp terminals, solid cable without cable end 1 x 0.51 x 1.5 mm² / AWG 20AWG 16 screw clamp terminals, flexible cable with cable end 2 x 0.52 x 2.5 mm² / AWG 20AWG 14 screw clamp terminals, solid cable without cable end 2 x 0.52 x 1.5 mm² / AWG 20AWG 16 	
IP degree of protection	IP20 conforming to IEC 60529	
Dielectric strength	2500 V	
Standards	IEC 61984	
Product certifications	UL CSA	
Marking	CE	

Ambient air temperature for storage	-4085 °C
Ambient air temperature for operation	-4055 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.000 cm
Package 1 Width	5.000 cm
Package 1 Length	8.500 cm
Package 1 Weight	96.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	6.400 cm
Package 2 Width	8.500 cm
Package 2 Length	25.400 cm
Package 2 Weight	1.012 kg
Unit Type of Package 3	S03
Number of Units in Package 3	110
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	11.645 kg

Contractual warranty

Warranty 12 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

⊘ Environmental footprint		
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	1	

Use Better

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
China RoHS Regulation	China RoHS declaration


Use Again


○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Take-back	No

Dimensions Drawings

Dimensions

mm in.






- (1) Relays
- (2) Protection module
- (3) Maintaining clamp

Connections and Schema

Wiring Diagram



Symbols shown in blue correspond to Nema marking.

Technical Illustration

Dimensions

