

MTS BALLAST 2.0 FLS

SKU: 6270612

S7S WR HI CI FO LG HRO SR



HEAVY-DUTY PROTECTION FOR YOUR FEET

If you work on an industrial environment where your feet are exposed to various risks every day, you know how important it is to wear the right footwear. Committed to helping workers' feet stay safe and comfortable on the job, we have designed Ballast 2.0, the new safety footwear for industrial workers from MTS.

MTS Ballast 2.0 Fast Lacing System (FLS) is the result of our extensive research and innovation in the field of safety footwear. We designed the shoes to help protect feet from a wide range of hazards, such as heavy objects, sharp materials, slippery surfaces, extreme temperatures and electric shocks – while providing comfort and stability on the job.

Built to meet the requirements of the latest EN standards, this new version of safety footwear incorporates a breathable and waterproof Sympatex® membrane and a Fast Lacing System (FLS). These additions aim to provide superior breathability, all-day comfort, improved protection, and a design that's adapted to the challenges of an industrial environment.

FEATURES

- High-quality full-grain leather upper
- Breathable and waterproof Sympatex® membrane
- Dual density PU/Nitrile sole, with orange phosphorescent inserts which provide day and night high visibility
- Non-metallic penetration protection insole
- Composite toe cap
- Fast Lacing System (FLS)
- Artico lining for increased abrasion, higher elasticity, improved heat conductivity for optimum work conditions
- Heel stiffener to reinforce the heel seat and provide optimum support to ankle region
- Reflective strips on the sides
- HI and CI markings: resistance to inimical environments - Heat Insulation and Cold Insulation of the sole complex
- HRO marking: resistance to hot contact
- Antistatic insole



MTS Ballast 2.0 Fast Lacing System (FLS) (SKU: 6270612)



TECHNICAL SPECIFICATIONS

Markings	S7S WR HI CI FO LG HRO
Sizes	35-49
Standard	EN ISO 20345:2022, S7S
EU Certificate	Tested and certified to latest EN standard: EN 20345:2022
Upper	High-quality full-grain leather upper with waterproof Sympatex® lining
Lining	Black colour full Ártico lining
Toe cap	Composite toe cap resistant to an impact of 200 Joules
Lacing system	Fast Lacing System (FLS)
Ankle Protection	Tested to latest EN standard
Mid sole	Anti-perforation, non-metallic onPROTECTOR DIAMOND, type PS
Insock	Thermoformed PU foam, Antistatic
Sole	PU/NITRILE HRO 300°C, oil resistant FO, antistatic, ESD and Heat Resistant
Energy absorption	Left: 33 J, Right: 33 J
Weight (size 42)	1,600 g - per pair



Antistatic
properties



Anti-puncture resistance
with PS level



Ankle
Protection



Composite toe cap



Resistance
to fuel oil



Heat resistance
outsole



Heel energy
absorption

sympatex®

ORDERING INFORMATION

DESCRIPTION	REF. IN SAP	SIZE
MTS Ballast 2.0 FLS	6270612	35-49

MTS SAFETY PRODUCTS UNITED KINGDOM

Honeywell House, Skimped Hill Lane,
Bracknell, Berkshire RG12 1EB
Phone: +44 (0) 1256 274938
Email: info-uk.hsp@honeywell.com

ANNIC S.A.S.

1 rue des Usines
82250 Laguepie – France
Tel.: +33 (0) 563 302 101
Fax.: +33 (0) 563 314 018
Email : contact@mts-morethansafety.com

MTS SAFETY PRODUCTS NORDIC AB

Box 15 147
SE-167 15 Bromma – Sverige
Phone: +46 (0) 424480433
Email: info-nordic.hsp@honeywell.com

For More Information

automation.honeywell.com

For Information on Innovations and Patents

hsmpats.com

MTS SAFETY PRODUCTS BENELUX BV

Lange Amerikaweg 55
7332 BP Apeldoorn, Nederland
Tel: +31 (0) 20 5656 988
Email: info-benelux.hsp@honeywell.com

