


TECHNICAL DATASHEET

HAS945



1. Back carrier – 0.1mm Black PVC
2. Adhesive Coating: 0.07mm \pm 0.01mm
3. Paper Liner: 0.17mm \pm 0.01mm
4. Adhesive tape: Acrylic PSA
5. Adhesive (to SUS): 1.5kg / 25mm \uparrow
6. Tensile Strength (woof) : 6kg / 25mm \uparrow
7. Tensile strength (warp): 13kg / 25mm \uparrow
8. Temperature range: -5°C - 50°C
9. Resistance to water: Good
10. Resistance to solvents: Fair

Unless stated otherwise all values given are average. All of the tapes in our range should be thoroughly tested on the substrates in the particular application they are intended for. Hi-Bond Tapes Ltd. will not be responsible for product failure unless full testing has been completed. The customer has to decide on the tapes suitability for the intended application.