



fitted with
work equipment
connected load
power consumption
glare-free
system of protection
class of protection
technology
usage
luminaire body

weight (net)
mains lead

design
fastening
special features

12 x Light-emitting diode
electronic plug-in transformer
100-240 V; 50/60 Hz
approx. 15 W
conical prismatic screen
IP 20
II
continuously dimmable
push button
sectional aluminium, anodised, aluminium coloured
anodised
approx. 0.9 kg
approx. 4,0 m; mains plug
CEE 7/XVI
mounted version
screw-down bracket; horizontal
pivot arm




CEE 7/XVI

illuminance

Comment: d=50cm

Em: 563 lx
Emax: 1569 lx
Emin: 83 lx



luminous intensity

