



Main

Range	TeSys
Device short name	VZN
Product or component type	Additional pole
Performance level	Standard
Poles description	1P
Contacts type and composition	1 NO
Product compatibility	VN12
Network type	AC DC
Network frequency	50/60 Hz
Mounting location	Right Left






Complementary

Range compatibility	TeSys VARIO VCFN switch disconnecter
[Ue] rated operational voltage	690 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	6 kV
[Ith] conventional free air thermal current	12 A
[Ithe] conventional enclosed thermal current	10 A
Mechanical durability	50000 cycles
Electrical durability	30000 Cycles DC-1...5 50000 cycles AC-21
Suitability for isolation	Yes
Connections - terminals	Power circuit: screw clamp terminals 4 mm ² - flexible - with cable end Power circuit: screw clamp terminals 4 mm ² - solid
Tightening torque	Power circuit: 0.7 N.m - on screw clamp terminals
Height	45.5 mm
Width	12 mm
Depth	39 mm
Net weight	0.02 kg

Environment

Standards	IEC 60947-3
Product certifications	GL UL CSA
Protective treatment	TC
IP degree of protection	IP20 conforming to IEC 60529
Mechanical robustness	Vibrations 10...150 Hz (5 gn) conforming to IEC 60068-2-6 Shocks 11 ms (15 gn) conforming to IEC 60068-2-27
Ambient air temperature for operation	-20...50 °C
Fire resistance	960 °C conforming to IEC 60595-2-1

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------