



## Grinding wheel E 125x7.2x22.23 mm Universal Line PSF STEEL for steel (10)

Grinding wheel E 125x7.2x22.23 mm Universal Line PSF STEEL for steel (10)

Item number: 62012634

EAN: 4007220471142

The entry-level range Universal Line PSF includes robust tools for processing the most common materials. Universal Line PSF tools achieve good results with high economic efficiency.

Grinding wheel for steel with high grinding performance and good tool life.

### Technical information

Abrasive	Aluminium oxide A
Dia. external	125 mm
Dia. hole	22.23 mm
Dia. hole, additional	without
Max. RPM	12200 RPM
Mounting system	Centre hole
PFERD TOOLS type	E 125-7 PSF STEEL
Shape	E / 27 / T27
Width	7.2 mm

### Advantages

- ✔ Fast work progress and high economic efficiency thanks to the high grinding performance.
- ✔ Good tool life.
- ✔ Also suitable for low-power angle grinders. Soft grinding characteristics, achieves particularly high stock removal rates even at low contact pressure.

**Materials that can be worked**

- ✓ Cast iron
- ✓ Steel

---

**Applications**

- ✓ Chamfering
- ✓ Deburring
- ✓ Grouting
- ✓ Surface grinding
- ✓ Work on fillet welds
- ✓ Work on weld seams

---

**Drive types**

- ✓ Angle grinder
  - ✓ Drive spindle
- 



August Rüggeberg GmbH & Co. KG  
Hauptstraße 13  
51709 Marienheide

+49 2264 9-0

+49 2264 9-400

[info@pferd.com](mailto:info@pferd.com)