

Siemens
EcoTech



SIMATIC ET 200SP HA, digital input module, DI 16x24VDC HA, suitable for terminal block H1, M1, color code CC01, channel diagnostics

General information	
Product type designation	DI 16x24VDC HA
Firmware version	V1.0
<ul style="list-style-type: none"> FW update possible 	Yes
Usable terminal block	type H1, M1, N0, H0, M0 (for details see the system manual)
Color code for module-specific color-coded label	CC01
Product function	
<ul style="list-style-type: none"> I&M data 	Yes; I&M0 to I&M3
Engineering with	
<ul style="list-style-type: none"> STEP 7 TIA Portal configurable/integrated from version 	V16
<ul style="list-style-type: none"> STEP 7 configurable/integrated from version 	V5.6
<ul style="list-style-type: none"> PCS 7 configurable/integrated from version 	V9.0
<ul style="list-style-type: none"> PCS neo can be configured/integrated from version 	V3.0
<ul style="list-style-type: none"> PROFINET from GSD version/GSD revision 	GSDML V2.3
Operating mode	
<ul style="list-style-type: none"> DI 	Yes
<ul style="list-style-type: none"> Counter 	No
<ul style="list-style-type: none"> Oversampling 	No
<ul style="list-style-type: none"> MSI 	No
Redundancy	
<ul style="list-style-type: none"> Redundancy capability 	Yes; With TB type M1
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
Input current	
Current consumption (rated value)	60 mA; without sensor supply
Current consumption, max.	120 mA; without sensor supply
Encoder supply	
Number of outputs	16
Output voltage, min.	18.2 V; L+ (-1 V)
Short-circuit protection	Yes; electronic (response threshold 0.7 A to 1.3 A; for IO redundancy up to 2.6 A) Ensure sufficient low-resistance cable routing to the sensor/actuator in order to attain the response threshold. Depending on the cable cross-section used, there may be constraints regarding the usable length of cable
Output current	

<ul style="list-style-type: none"> • up to 60 °C, max. 	2 A; 1 A when mounted vertically; see derating information in Equipment Manual
<ul style="list-style-type: none"> • up to 70 °C, max. 	1 A; See derating information in Equipment Manual
24 V encoder supply	
<ul style="list-style-type: none"> • 24 V 	Yes
<ul style="list-style-type: none"> • Short-circuit protection 	Yes; electronic (response threshold 0.7 A to 1.3 A; for IO redundancy up to 2.6 A) Ensure sufficient low-resistance cable routing to the sensor/actuator in order to attain the response threshold. Depending on the cable cross-section used, there may be constraints regarding the usable length of cable
<ul style="list-style-type: none"> • Output current per channel, max. 	0.5 A
<ul style="list-style-type: none"> • Output current per module, max. 	2 A
Power	
Power consumption from the backplane bus	80 mW
Power loss	
Power loss, typ.	3.6 W; Maximum value (taking the max. encoder current and the max. operating voltage into account)
Address area	
Address space per module	
<ul style="list-style-type: none"> • Address space per module, max. 	2 byte; + 2 bytes for QI information (additional 18 bytes when using high-precision time stamping)
Hardware configuration	
Automatic encoding	
<ul style="list-style-type: none"> • Mechanical coding element 	Yes
Digital inputs	
Number of digital inputs	16
Digital inputs, parameterizable	Yes
Sourcing/sinking input	Yes; P-reading
Input characteristic curve in accordance with IEC 61131, type 1	Yes
Input characteristic curve in accordance with IEC 61131, type 2	No
Input characteristic curve in accordance with IEC 61131, type 3	Yes
Pulse extension	Yes
<ul style="list-style-type: none"> • Length 	off, 50 ms, 100 ms, 200 ms, 500 ms, 1 s, 2 s
Time stamp	Yes; Resolution 10 ms
Time stamp (with precision of 1 ms)	Yes; Resolution 1ms
Edge evaluation	Yes; rising edge, falling edge, edge change
Input voltage	
<ul style="list-style-type: none"> • Rated value (DC) 	24 V
<ul style="list-style-type: none"> • for signal "0" 	-30 to +5 V
<ul style="list-style-type: none"> • for signal "1" 	+11 to +30V
Input current	
<ul style="list-style-type: none"> • for signal "1", typ. 	2.5 mA
Input delay (for rated value of input voltage)	
for standard inputs	
— parameterizable	Yes; none / 0.05 / 0.1 / 0.4 / 0.8 / 1.6 / 3.2 / 12.8 / 20 ms
Cable length	
<ul style="list-style-type: none"> • shielded, max. 	1 000 m
<ul style="list-style-type: none"> • unshielded, max. 	600 m
Encoder	
Connectable encoders	
<ul style="list-style-type: none"> • 2-wire sensor 	Yes
— permissible quiescent current (2-wire sensor), max.	1.5 mA
Interrupts/diagnostics/status information	
Diagnostics function	Yes
Alarms	
<ul style="list-style-type: none"> • Diagnostic alarm 	Yes; channel by channel
<ul style="list-style-type: none"> • Hardware interrupt 	Yes; channel by channel
Diagnoses	
<ul style="list-style-type: none"> • Diagnostic information readable 	Yes
<ul style="list-style-type: none"> • Monitoring the supply voltage 	Yes; Module-wise
— parameterizable	Yes

<ul style="list-style-type: none"> Monitoring of encoder power supply Wire-break 	<p>Yes</p> <p>Yes; Channel-by-channel, optional protective circuit for preventing wire-break diagnostics in the case of simple encoder contacts: 15 kOhm to 18 kOhm</p> <p>Yes; Encoder supply to M, channel by channel</p>
Diagnostics indication LED	
<ul style="list-style-type: none"> MAINT LED Monitoring of the supply voltage (PWR-LED) Channel status display for channel diagnostics for module diagnostics 	<p>Yes; Yellow LED</p> <p>Yes; green PWR LED</p> <p>Yes; green LED</p> <p>Yes; red LED</p> <p>Yes; green/red LED</p>

Potential separation	
Potential separation channels	
<ul style="list-style-type: none"> between the channels between the channels and backplane bus between the channels and the power supply of the electronics 	<p>No</p> <p>Yes</p> <p>No</p>

Isolation	
Isolation tested with	1 500 V DC/1 min, type test

Ambient conditions	
Ambient temperature during operation	
<ul style="list-style-type: none"> horizontal installation, min. horizontal installation, max. vertical installation, min. vertical installation, max. 	<p>-40 °C</p> <p>70 °C</p> <p>-40 °C</p> <p>60 °C</p>

Dimensions	
Width	22.5 mm
Height	115 mm
Depth	138 mm

Weights	
Weight, approx.	135 g

Classifications			
		Version	Classification
	eClass	14	27-24-26-04
	eClass	12	27-24-26-04
	eClass	9.1	27-24-26-04
	eClass	9	27-24-26-04
	eClass	8	27-24-26-04
	eClass	7.1	27-24-26-04
	eClass	6	27-24-26-04
	ETIM	10	EC001599
	ETIM	9	EC001599
	ETIM	8	EC001599
	ETIM	7	EC001599

Approvals / Certificates

General Product Approval



[Miscellaneous](#)



[China RoHS](#)



General Product Approval **For use in hazardous locations**



[Declaration of Con-
formity](#)



For use in hazardous locations	Maritime application				
--------------------------------	----------------------	--	--	--	--



[Miscellaneous](#)



Maritime application				Environment	
----------------------	--	--	--	-------------	--



[NK / Nippon Kaiji Kyokai](#)



[CCS \(China Classification Society\)](#)



last modified:

11/24/2025