

SAC-6P-M12MSM/ 1,5-PUR PE - Power cable



1414949

<https://www.phoenixcontact.com/gb/products/1414949>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Power cable, 6-position, PUR halogen-free, black-gray RAL 7021, Plug straight M12, coding: M, on free cable end, cable length: 1.5 m, for AC current up to 8 A/690 V

Your advantages

- Easy and safe: 100 % electrically tested plug-in components
- Protection against mismatching, thanks to special M-coding
- Our standard: robust halogen-free PUR cable

Commercial data

Item number	1414949
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF1CGP
Product key	BF1CGP
Catalog page	Page 298 (C-2-2019)
GTIN	4055626035765
Weight per piece (including packing)	250.03 g
Weight per piece (excluding packing)	250.03 g
Customs tariff number	85444290
Country of origin	PL

SAC-6P-M12MSM/ 1,5-PUR PE - Power cable



1414949

<https://www.phoenixcontact.com/gb/products/1414949>

Technical data

Product properties

Product type	Power cable
Application	Power supply
Number of positions	6
No. of cable outlets	1
Shielded	no
Coding	M

Data management status

Article revision	07
------------------	----

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	V0
Material of grip body	PP
Contact material	CuZn
Contact surface material	Ni/Au
Contact carrier material	PA
Material for screw connection	Zinc die-cast, nickel-plated

Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	690 V AC
Nominal current I_N	8 A

Connector

Connection 1

Type	Plug straight M12
Coding type	M (Power)

Connection 2

Type	free cable end
------	----------------

Cable/line

Cable length	1.5 m
--------------	-------

PUR halogen-free black [PUR]

SAC-6P-M12MSM/ 1,5-PUR PE - Power cable



1414949

<https://www.phoenixcontact.com/gb/products/1414949>

Dimensional drawing	
Cable weight	130 kg/km
Number of positions	6
Shielded	no
Cable type	PUR halogen-free black [PUR]
Conductor cross section	6x 1.5 mm²
Wire diameter incl. insulation	2.35 mm ±0.1 mm
External cable diameter	8.80 mm ±0.25 mm
Outer sheath, material	PUR
External sheath, color	black-gray RAL 7021
Conductor material	Bare Cu litz wires
Material wire insulation	PP
Single wire, color	black 1, black 2, black 3, black 4, black 5, green/yellow
Thickness, insulation	≥ 0.36 mm
Thickness, outer sheath	approx. 0.90 mm
Max. conductor resistance	≤ 14.1 Ω/km (at 20 °C)
Insulation resistance	≥ 1 GΩ*km (at 20 °C)
Nominal voltage, cable	≤ 1000 V AC
Test voltage	≥ 3000 V AC (Spark test)
Minimum bending radius, fixed installation	5 x D
Minimum bending radius, flexible installation	10 x D
Smallest bending radius, fixed installation	44 mm
Smallest bending radius, movable installation	88 mm
Dynamic load capacity (bending)	Max. bending cycles: 4000000, Bending radius: 10xD, Traversing path: 10 m, Traversing rate: 3 m/s, Acceleration: 10 m/s²
Halogen-free	in accordance with DIN VDE 0472 part 815 according to DIN EN 60754-1
Flame resistance	in accordance with UL 758/1581 FT2 according to DIN EN 60332-2-2
Resistance to oil	according to DIN EN 60811-404, 168 h at 100 °C
Other resistance	Hydrolysis and microbe resistant as per VDE 0282 section 10 Low adhesion abrasion-resistant Resistant to salt water
Ambient temperature (operation)	-50 °C ... 85 °C (cable, fixed installation) -30 °C ... 85 °C (Cable, flexible installation)

SAC-6P-M12MSM/ 1,5-PUR PE - Power cable



1414949

<https://www.phoenixcontact.com/gb/products/1414949>

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67 (without preloading, as additional test in accordance with IEC 60529)
Ambient temperature (operation)	-25 °C ... 85 °C (Plug / socket)

Standards and regulations

Standard designation	M12 connector
Standards/specifications	IEC 61076-2-111

SAC-6P-M12MSM/ 1,5-PUR PE - Power cable


1414949

<https://www.phoenixcontact.com/gb/products/1414949>




Drawings

Schematic diagram



Pin assignment of M12 connector, 6-pos., M-coded, pin side view


Circuit diagram




SAC-6P-M12MSM/ 1,5-PUR PE - Power cable

1414949

<https://www.phoenixcontact.com/gb/products/1414949>



Current carrying capacity



Plug, M12 x 1, straight, shielded

SAC-6P-M12MSM/ 1,5-PUR PE - Power cable



1414949

<https://www.phoenixcontact.com/gb/products/1414949>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1414949>



UL Listed

Approval ID: E468743

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	600 V	10 A	-	- 16



cUL Listed

Approval ID: E468743

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	600 V	10 A	- 16	-



EAC-RoHS

Approval ID: RU D-DE.HB35.B.00387

cULus Listed

SAC-6P-M12MSM/ 1,5-PUR PE - Power cable



1414949

<https://www.phoenixcontact.com/gb/products/1414949>

Classifications

ECLASS

ECLASS-11.0	27060311
ECLASS-12.0	27060311
ECLASS-13.0	27060327

ETIM

ETIM 9.0	EC001855
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-6P-M12MSM/ 1,5-PUR PE - Power cable



1414949

<https://www.phoenixcontact.com/gb/products/1414949>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol(CAS: 119-47-1)
SCIP	c46e0430-b327-4fac-836e-70e563e419bb

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk