

FEATURES

- **Graphite material:** Offers excellent thermal conductivity and chemical resistance
- **Maximum operating pressure of 20000 kPa:** Suitable for high-pressure applications
- **Maximum operating temperature of 650 °C:** Ideal for high-temperature environments
- **Rotary speed of 30 m/s:** Supports high-speed operations
- **16mm section:** Provides robust sealing capability

RS PRO 8m Graphite Gland Packing, 16mm Section

RS Stock No: 606-568



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO gland packing is designed for high-performance sealing in industrial applications. Made from durable graphite, it is ideal for use in environments requiring high temperature and pressure resistance. The gland packing ensures reliable sealing, reducing maintenance needs and enhancing operational efficiency.

General Specifications

Maximum Operating Pressure	20000 kPa
Product Type	Gland & Valve Packing
Rotary Speed	30 m/s
Section	16 mm
Sub Type	Gland Packing

Mechanical Specifications

Length	8 m
Material	Graphite

Operation Environment Specifications

Maximum Operating Temperature	650 °C
-------------------------------	--------

Approvals

Standards/Approvals	ANSI-ESD S20.20:2021, RoHS
---------------------	----------------------------