


Part Number: 8728



Special Audio, 2 Pair 22 AWG TC, Shielded, CM

[Request Sample](#)

Product Description

Audio, 2 Pair 22 AWG stranded (7x30) TC conductors, polypropylene insulation, cabled in pairs, overall Beldfoil® shield (100% coverage), 24 AWG stranded TC drain wires, CM, PVC jacket.

Technical Specifications

Product Overview

Environmental Space:	Indoor (Not Riser or Plenum)
Suitable Applications:	Special Audio, Communication and Instrumentation Cable

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Pairs
22	7x30	TC - Tinned Copper	0.03 in	2

Conductor Count:	4
Total Number of Pairs:	2
Conductor Size:	22 AWG

Insulation

Material	Nominal Diameter
PP - Polypropylene	0.05 in

Color Chart

Number	Color
1	Black & Red
2	White & Green

Inner Shield Material

Type	Layer	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Layer 1	Aluminum Foil-Polyester Tape	Beldfoil®	100 %	TC - Tinned Copper	24	Stranded
Tape	Layer 2	Polyester Tape		100 %		TC - Tinned Copper	

Outer Shield Material

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Aluminum/Polyester	Beldfoil®	100 %	TC - Tinned Copper	24	Stranded mm

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.215 in	0.028 in

Electrical Characteristics

Conductor DCR

Individual Pair Nominal Shield DCR	Nominal Conductor DCR
16.6 Ohm/1000ft	17 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
35 pF/ft	62 pF/ft

Inductance

Nominal Inductance
0.18 µH/ft

Impedance

Nominal Characteristic Impedance
50 Ohm

Delay

Nominal Velocity of Propagation (VP) [%]
66 %

Current

Max. Recommended Current [A]
2.3 Amps per conductor @ 25°C

Voltage

UL Voltage Rating
300 V RMS (UL AWM Style 2717)

Temperature Range

UL Temp Rating:	80°C (UL AWM Style 2717)
Operating Temp Range:	-20°C To +80°C

Mechanical Characteristics

Bulk Cable Weight:	28 lbs/1000ft
Max Recommended Pulling Tension:	36.4 lbs
Min Bend Radius/Minor Axis:	2.25 in

Standards

NEC Articles:	800
NEC/(UL) Specification:	CM
CEC/C(UL) Specification:	CM
UL AWM Style:	UL Style 2717 (300 V 80°C)
CPR Euroclass:	Eca

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Flammability, LSOH, Toxicity Testing

UL Flammability:	UL1685 UL Loading
UL voltage rating:	300 V RMS (UL AWM Style 2717)

Plenum/Non-Plenum

Plenum (Y/N): No

Part Number

Variants

Item #	Color	Footnote
8728 0601000	Chrome	C
8728 060500	Chrome	C
8728 0605000	Chrome	C
8728 060U1000	Chrome	
8728 060U500	Chrome	
8728 0605000	Chrome	

Footnote: C - CRATE REEL PUT-UP.

Product Notes

Notes: Each pair Beldfoil« shielded with individual drain wire plus a polyester film over each shield.

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.