







- 1 OBSOLETE PART NO.
- 2 "AMP", PART NO. AND DATE CODE MARKED (WHITE),
.062±.015 CHARS. WHEN HOUSING SIZE PERMITS
- 3 .046±.015 CHARS. MARKED (WHITE) FIRST AND
EVERY 5TH CAVITY, ONE SIDE.
- 5 SUPERSEDED BY 3-87456-3.
- 6 SUPERSEDED BY 4-87456-5.
- 7 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



SUP BY 1-87456-7

	6-87456-5	81.28 [3.200]	31	64	6-87456-6
7	6-87456-3	73.66 [2.900]	28	58	6-87456-4
7	6-87456-1	71.12 [2.800]	27	56	6-87456-2
	5-87456-9	60.96 [2.400]	23	48	6-87456-0
7	5-87456-7	83.82 [3.300]	32	66	5-87456-4
7	5-87456-5	88.90 [3.505]	34	70	5-87456-6
	5-87456-3	2.67 [.105]	-	2	-
	5-87456-1	76.33 [3.005]	29	60	5-87456-2
	4-87456-9	5.21 [.205]	1	4	5-87456-0
	4-87456-7	91.57 [3.605]	35	72	4-87456-8
	4-87456-5	68.71 [2.705]	26	54	4-87456-6
	4-87456-3	53.47 [2.105]	20	42	4-87456-4
	4-87456-1	66.17 [2.605]	25	52	4-87456-2
	3-87456-9	63.63 [2.505]	24	50	4-87456-0
	3-87456-7	56.01 [2.205]	21	44	3-87456-8
	3-87456-5	50.93 [2.005]	19	40	3-87456-6
	3-87456-3	48.39 [1.905]	18	38	3-87456-4
	3-87456-1	45.85 [1.805]	17	36	3-87456-2
	2-87456-9	43.31 [1.705]	16	34	3-87456-0
	2-87456-7	40.77 [1.605]	15	32	2-87456-8
	2-87456-5	38.23 [1.505]	14	30	2-87456-6
	2-87456-3	35.69 [1.405]	13	28	2-87456-4
	2-87456-1	33.15 [1.305]	12	26	2-87456-2
	1-87456-9	30.61 [1.205]	11	24	2-87456-0
7	1-87456-7	28.07 [1.105]	10	22	1-87456-8
	1-87456-5	25.53 [1.005]	9	20	1-87456-6
	1-87456-3	22.99 [.905]	8	18	1-87456-4
	1-87456-1	20.45 [.805]	7	16	1-87456-2
	87456-9	17.91 [.705]	6	14	1-87456-0
	87456-7	15.37 [.605]	5	12	87456-8
	87456-5	12.83 [.505]	4	10	87456-6
	87456-3	10.29 [.405]	3	8	87456-4
	87456-1	7.75 [.305]	2	6	87456-2
	PART NO. WITHOUT MARKING	C	A	NO. OF POSITIONS	PART NO. MARKED

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG E. BRANDBERG 11-06-92		 TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK J. GESFORD 11-30-92			
		APVD J. GESFORD 11-30-92		NAME HOUSING, MOD IV DOUBLE ROW, .100X.100 C/L CRIMP SNAP-IN, SHORT ENTRY	
		PRODUCT SPEC			
		—			
		APPLICATION SPEC			
MATERIAL GLASS FILLED NYLON COLOR BLACK PER ASTM D4066		FINISH —		WEIGHT —	
DIMENSIONS: mm [INCHES]		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		SIZE A1	
0 PLC ± — 2 PLC ± — 3 PLC ± .02 4 PLC ± .005 ANGLES ± 0° 30'		PRODUCT SPEC — APPLICATION SPEC —		DRAWING NO C-87456	
CUSTOMER DRAWING		SCALE 4:1		SHEET 1 of 1	
REV P2		REV P2		REV P2	