




Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Type: **PCB Mount Header**

PCB Mount Orientation: **Vertical**

Connector System: **Wire-to-Board**

Number of Positions: **12**

Number of Rows: **3**

Features

Product Type Features

Mixed & Hybrid Header	No
Connector Shape	Rectangular
PCB Connector Type	PCB Mount Header
Connector System	Wire-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Connector Product Type	Connector Assembly

Configuration Features

Number of Columns	4
Number of Loaded Positions	12
Number of Power Positions	12
Connector Contact Load Condition	Fully Loaded
PCB Mount Orientation	Vertical
Number of Positions	12



Number of Rows	3
Electrical Characteristics	
Operating Voltage	600 VAC
Body Features	
Primary Product Color	Natural
Contact Features	
Contact Underplating Material	Nickel
Contact Underplating Material Thickness	1.27 – 1.79 µm[50 – 70 µin]
Contact Size	2.95mm
Contact Mating Area Plating Material Thickness	3.81 – 5.08 µm[150 – 200 µin]
PCB Contact Termination Area Plating Material Thickness	3.81 – 5.08 µm[150 – 200 µin]
Contact Shape & Form	Round
Contact Layout	Matrix
Contact Base Material	Phosphor Bronze
PCB Contact Termination Area Plating Material	Pre-Tin
Contact Mating Area Plating Material	Pre-Tin
Contact Type	Socket
Contact Current Rating (Max)	12 A
Termination Features	
Termination Post & Tail Diameter	1.57 mm[.062 in]
Termination Post & Tail Length	5.09 mm[.2 in]
Termination Method to PCB	Through Hole - Solder
Mechanical Attachment	
Panel Mount Feature	Without
Mating Retention Type	Locking Tab
Mating Retention	With
Mating Alignment Type	Polarization
PCB Mount Retention	Without
PCB Mount Alignment	Without
Connector Mounting Type	Board Mount
Mating Alignment	With
Housing Features	



Mating Entry Location	Top
Housing Material	Nylon
Centerline (Pitch)	6.35 mm[.25 in]

Dimensions

Row-to-Row Spacing	6.35 mm[.25 in]
Connector Width	20.32 mm[.8 in]
PCB Thickness (Recommended)	3.18 mm[.125 in]
Connector Height	13.97 mm[.55 in]
Connector Length	26.67 mm[1.05 in]
Profile Height from PCB	14.73 mm[.58 in]

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

Compatible With Agency/Standards Products	CSA, UL, VDE
UL Rating	Recognized
Compatible With Approved Standards Products	UL E28476
Glow Wire Rating	Standard Part - Not Glow Wire
UL Flammability Rating	UL 94V-2

Packaging Features

Packaging Quantity	94
Packaging Method	Carton

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247)



Candidate List Declared Against: JAN 2025
(247)
Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process CapabilityWave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2178620-1
UMNL 12 WAY CAP HOUSING



TE Part # 794280-1
12P UMNL WIRE SEAL



TE Part # 1-640723-0
12P UMNL STR/REL & INSRT NATL



TE Part # 1586854-1
12P UMNL CAP HSG, GW



TE Part # 1-480708-0
12P UMNL PLUG HSG NATL



TE Part # 640717-1
12P UMNL STR/REL



TE Part # 2178621-1
UMNL 12 WAY CAP HOUSING



TE Part # 1863006-1
12P UMNL CAP HSG



TE Part # 1-350590-0
STR/REL CLAMP NATL



TE Part # 794727-1
12P UMNL CAP HSG NATL, BLACK



TE Part # 643255-1
12P UMNL ASSY MOD HSG VO



TE Part # 350812-1
STR/REL CLAMP UMNL



TE Part # 926681-3
12P UNIV.CAP HSG.



TE Part # 926681-1
UNIV.M-N-L.CAP HSG.



TE Part # 794279-1
12P UMNL INTERFACE SEAL

Also in the Series | Universal MATE-N-LOK



Circular Power Connectors(2)



Connector Caps & Covers(34)




Connector Seals & Cavity Plugs(27)



Connector Strain Relief(7)



Insertion & Extraction Tools(4)




PCB Headers & Receptacles(286)



Rectangular Power Connectors(651)



Standard Circular Connectors(1)




Wire-to-Board Headers & Receptacles
(286)


Customers Also Bought



TE Part #1-2356631-1
3POS,MCON 1.2,TAB HSG ASSY,SLD,
COD A



TE Part #1-2378191-1
15POS,HYBRID,HDR ASSY,180DEG,
COD A



TE Part #5406721-2
MJ,RJ45,SM,TGRAY,13"REEL



TE Part #1879452-3
TE 750W 1R5 5% Bracket



TE Part #6-104809-1
12 MTE HDR SRST LATCH W/HLDWN



TE Part #84953-4
1MM FPC HORZ.TOP CONT.ASSY 4P




TE Part #225679-E
POWELM STIFT VOLL M8 13 2,54 *
EP 7,5 *



TE Part #1-2356607-1
3POS,MCON 1.2,REC HSG ASSY,SLD,
COD A



TE Part #1977067-1
FSMMSH=R/A TACT SWITCH, SMT W
/OUT PEGS



TE Part #640502-3
12P MR HDR ASSY V0

Documents

Product Drawings

12P UMNL HDR ASSY LNG/TL

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_350991-4_M.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_350991-4_M.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_350991-4_M.3d_stp.zip

English

Customer View Model

ENG_CVM_350991-4_G1.3d_igs.zip

English



Customer View Model

[ENG_CVM_350991-4_G1.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_350991-4_G1.2d_dxf.zip](#)

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[SOFT_SHELL_PIN_SOCKET_CONNECTORS_STANDARD_DENSITY](#)

English

Product Specifications

[Application Specification](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

Agency Approvals

[UL](#)

English