



FLAMESTAT HIGH VIS WINTER JACKET WOMAN CLASS 3 4285 ATHS

ART. NO: 129548

Dirt, oil and water-repellent / Fully lined with fleece in body and silky and soft quilted lining in sleeve / Reflective detailing on shoulders / Front placket opening with zip to top of collar and concealed snap fastening / Fleece-lined collar with snap fastening for attachable hood, 125064 / Bellowed chest pocket with concealed snap fastening, inside D-ring and pen strap / Chest pocket with zip / Concealed buttons and loop for sheath knife / Microphone holder / Map pocket with zip and inside mobile phone pocket accessible from outside / 2 fleece-lined front pockets with zip / Inside pocket with button / Inside mobile phone pocket with earpiece loop / Elastic cuffs inside sleeves / Extended back / Adjustable drawstring at hem / Zip in lining for easy embroidery and transfer / Approved according to EN 61482-1-2 APC 2, EN 61482-1-1 ELIM: 19 cal/cm² ATPV: 25 cal/cm², EN ISO 11612 A1 B1 C1 E2 F1, EN ISO 11611 A1 class 1, EN 1149-5, EN 13034 Type PB [6], EN ISO 20471 class 2 in sizes XS-S and class 3 in sizes M-3XL and EN 342 / Certified after 50 washes / Leasing laundry-tested according to ISO 15797 / OEKO-TEX® certified.

Material: 45% modacrylic, 35% cotton, 18% polyamide, 2% anti-static fibre, dirt, oil and water repellent. Fleece lining 50% modacryl, 30% cotton, 18% polyester, 2% anti-static fibre. Silky quilted lining 40% modacrylic, 37% viscose FR, 22% viscose, 1% anti-static fibre. In transition to PFAS free.

Weight: Outer fabric 300 g/m², fleece lining 370 g/m², silky quilted lining 260 g/m².

Color: F171 High vis Yellow/Navy

Size: XS-3XL



EN 11612



EN 11611



EN 1149-5



IEC 61482-2



EN 13034



EN 20471



EN 342



FRISTADS®

SIZES MAY VARY BETWEEN COLORS
Print date: 2025-09-04