


FEATURES

- **Annealed Copper Conductor:** Provides superior electrical conductivity and flexibility.
- **Polyvinyl Chloride Jacket:** Offers robust protection against environmental factors and mechanical stress.
- **Temperature Range -15 °C to 90 °C:** Suitable for a wide range of operating conditions.
- **Voltage Rating of 500 V:** Ensures compatibility with standard electrical systems.
- **Plain Conductor Type:** Simplifies installation and maintenance.
- **24/0.2 Core Strands:** Enhances flexibility and ease of handling.
- **White Jacket Colour:** Facilitates easy identification and aesthetic integration.

RS PRO 0.75 mm² Flexible Cable, 100 m Length

RS Stock No: 606-109



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO flexible cable is designed for reliable electrical connections in various industrial and commercial applications. With a conductor made from annealed copper, it ensures excellent conductivity and durability. The cable is suitable for installations requiring flexibility and is ideal for environments with temperature variations.

General Specifications

Conductor Material	Annealed Copper
Conductor Type	Plain
Jacket Colour	White
Product Type	Flexible Cable

Mechanical Specifications

Cable CSA	0.75 mm ²
Cable Length	100 m
Core Strands	24/0.2
Jacket Material	Polyvinyl Chloride
Number of Cores	2
Outside Diameter	7.2 mm

Operation Environment Specifications

Maximum Operating Temperature	90 °C
Minimum Operating Temperature	-15 °C

Approvals

Standards/Approvals	ACI, BASEC ISO 9001 UKAS CS1-029, BS EN 50363-3, BS EN 50363-4-1, BS EN 50525-2-11, BS EN 60228
---------------------	---

Electrical Specifications

Voltage	500 V
---------	-------