


Cable label, self laminating, white/transparent, thermal transfer print, 39.87x31.75mm, H2=134.62mm, 650pcs.

Art.-No. 596-01904 | TAG32-135TD1-1232-CL/WH | 




- High-quality self-laminating labels made of polyester
- Suitable for marking of wires and cables in harsh environments
- Flexible but also tear and impact resistant material
- Excellent resistance to alcohol, gasoline, cleaning agents and hydraulic oils
- Very temperature and UV-resistant
- Perforation allows demand-based shortening of the protective laminate for smaller outer diameters
- Laminating function gives excellent protection against
-



More products in this product group:

[Self-laminating labels, thermal transfer >](#)

Application	These self-laminating labels are ideal for marking hoses and pipes in harsh environments, e.g. as they can be found in the hydraulics industry. Helatag 1232 consists of a white printable area with a protective laminate ensure the printed text is shielded from negative environmental influences - such as humidity, dirt, debris and mechanical abrasion.
Cable ø max	30.24 mm
Cable ø min	14.01 mm
Chem. Material Properties	Resistant to water, alcohol, most oils, greases, fuel, aliphatic solvents, weak acids, salts and alkalis.
Colour	White (WH), Transparent (CL)
Colour Marking Field	White (WH)
Fixation Method	Pasting / Stick
Material	Type 1232, Polyester, white transparent, self-laminating (1232)
Mech. material properties	Due to its flexibility particularly suitable for identification of cables.
PART DESCRIPTION	TAG32-135TD1-1232-CL/WH
Pack Content	650 pcs.
Package Content packed in	pack
Product Family	Helatag 1232
Product Group	Self-laminating labels, thermal transfer
Self adhesive (Yes/No)	Yes
Type	TAG32-135TD1
Variant	Roller form
With label space	Yes



Bundle ø max.	30.88 mm
Bundle ø min.	14.01 mm
H printable	39.87 mm
Height (H)	39.87 mm
Height (H2)	134.62 mm
Print Method	thermal transfer print
Thickness of Foil	50
Width (W)	31.75 mm
Width of LIner (WL)	1.49 "
Width of Liner (WL)	38.00 mm

Adhesive	Acrylic
Adhesive Operating Temperature	-40 °C to +150 °C
CE Certification	No
CSA Certified	No
Curing Temperature	from +2 °C
ELV compliant (Article 4 - 2)	YES
Halogen-free	Yes
Hazardous Goods	No
Operating Temperature	-40 °C to +150 °C
ROHS compliant	Yes
Recommended Ribbon Type	TT822OUT
Resistance to	Brake cleaner: 720h (at room temperature), Alcohol 94%: 720h (at room temperature), Hydraulic oil: 720h (at room temperature)
Specifications	HF✓ RoHS✓
UV-Stabilised	Yes



GTIN-13 / EAN	4031026622644
Labels per Column	1
Labels per Row	1 pc.
Packaging 1 - Height (m)	0.032 m
Packaging 1 - Length (m)	0.135 m
Packaging 1 - Qty	650
Packaging 1 - Type	reel
Packaging 1 - Volume (m³)	0.0005832 m³
Packaging 1 - Weight (kg)	0.61 kg
Packaging 1 - Width (m)	0.135 m
Packaging 3 - Height (m)	0.313 m
Packaging 3 - Length (m)	0.4 m
Packaging 3 - Qty	46800
Packaging 3 - Type	carton
Packaging 3 - Volume (m³)	0.0501 m³
Packaging 3 - Weight (kg)	44.445 kg
Packaging 3 - Width (m)	0.4 m
Packaging 4 - Length (m)	1.2 m
Packaging 4 - Type	pallet
Packaging 4 - Width (m)	0.8 m

More Information

UNSPSC Key	55121612
------------	----------

