

# Switching Power Supply Type SPD 10W DIN rail mounting

CARLO GAVAZZI



- Universal AC input full range
- Installation on DIN rail 7.5 or 15mm
- Short circuit protection
- Overload protection
- High efficiency
- LED indicator for DC power ON
- LED indication for DC low
- Power Ok output
- Internal input filter
- CE, TUV approved and cULus Listed

## Product Description

The Switching power supplies SPD series are specially designed to be used in all automation application where the installation is on a DIN rail and compact dimensions and performance are a must.

## Ordering Key

**SP D 24 10 1 B**

Model \_\_\_\_\_  
 Mounting ( D = Din rail ) \_\_\_\_\_  
 Output voltage \_\_\_\_\_  
 Output power \_\_\_\_\_  
 Input Type \_\_\_\_\_  
 Optional features \_\_\_\_\_

Input type: 1= single phase

## Approvals



## Optional Features

Description	Code
Spring connectors	B

## Output Performances

MODEL NO.	INPUT VOLTAGE	OUTPUT WATTAGE	OUTPUT VOLTAGE	OUTPUT CURRENT	EFF. (min.)	EFF. (typ.)
<b>Single Output Models</b>						
SPD05	90~264 VAC	10 WATTS	+ 5 VDC	2000 mA	71%	73%
SPD12	90~264 VAC	10 WATTS	+12 VDC	840 mA	73%	75%
SPD15	90~264 VAC	10 WATTS	+15 VDC	670 mA	74%	76%
SPD24	90~264 VAC	10 WATTS	+24 VDC	420 mA	74%	76%

## Output Data

Line regulation	± 1%	Rated continuous loading	5V Model	2A @ 5VDC/1.7A @ 5.75VDC		
Load regulation	± 2%		12V Model	0.84A@12VDC/0.72A@13.8VDC		
Minimum load	0	15V Model	0.67A @ 15VDC/0.58A @ 17.25VDC	Reverse voltage		
Turn on time (full resistive load)	1000ms	24V Model	0.42A @ 24VDC/0.34A @ 28.8VDC			
Vi nom, Io nom with 3500µF	1500ms	Capacitor load	3500µF			
Transient recovery time	2ms		Voltage rise time at (full resistive load)	500ms		
Ripple and noise	50mVpp			Vi nom, Io nom with 3500µF	150ms	
Output voltage accuracy	+ 1%					
Temperature coefficient	± 0.03%/°C					
Hold up time	25ms					
Voltage fall time (I <sub>o</sub> nom)	Vi= 115VAC					
	Vi= 230VAC					
	100ms					
	150ms max					

## Input Data

<b>Rated input voltage</b>	100 - 240VAC	<b>Power dissipation</b> (Vi : 230VAC, lo nom)	<b>5V Model</b> 4.0W <b>12V Model</b> 3.4W <b>15V Model</b> 3.3W <b>24V Model</b> 2.8W
<b>Voltage range</b>	<b>AC</b> 90 - 264VAC <b>DC</b> 120 - 375VDC	<b>Frequency range</b>	47- 63Hz
<b>Rated input current</b> (Vi : 115VAC, lo nom)	<b>Typ.</b> 200mA <b>Max.</b> 300mA	<b>Leakage current</b>	<b>Input-Output</b> 0.25mA <b>Input-FG</b> 3.5mA
<b>Inrush current</b>	<b>Vi= 115VAC</b> 10A <b>Vi= 230VAC</b> 18A		

## Controls and Protections

<b>Overload</b>	110 – 145%	<b>Over voltage protection</b>	125-145%
<b>Input fuse</b>	T2A/250VAC internal <sup>1)</sup>	<b>Internal surge voltage protection</b> (IEC 61000-4-5)	Varistor
<b>Output short circuit</b>	Hiccup mode		

<sup>1)</sup> Fuse not replaceable by user


## General Data (@ nominal line, full load, 25°C )

<b>Ambient temperature</b>	-20°C to 71°C	<b>MTBF</b> (Bellcore issue 6 @ 40°C, GB)	<b>5V Model</b> 801000 Hours <b>12V Model</b> 803000 Hours <b>15V Model</b> 805000 Hours <b>24V Model</b> 808000 Hours
<b>Derating (&gt;61°C to +71°C)</b>	2.5%/°C	<b>Case material</b>	Plastic: PC, UL94-V0
<b>Ambient humidity</b>	20 ~ 95%RH	<b>Pollution degree</b>	2
<b>Storage</b>	-25°C to +85°C	<b>Altitude</b>	2000m
<b>Protection degree</b>	IP20	<b>Dimensions LxWxD mm(inch)</b>	90(3.60)x22.5(0.89)x114(4.49)
<b>Cooling</b>	Free air convection	<b>Weight</b>	120g
<b>Insulation voltage</b>	<b>Input-Output</b> 3.000VAC/4242VDC min <b>Input-FG</b> 1.500VAC/2121VDC min		
<b>Insulation resistance I/O</b>	100MΩ min (@ 500VDC)		


## Norms and Standards

<b>Vibration resistance</b>	meet IEC 60068-2-6 (Mounting by rail: 10-500Hz, 2G, along X, Y, Z each Axis, 60 min for each Axis)	<b>CE</b>	EN 61000-6-3, EN 55022 Class B, EN 61000-3-2, EN 61000-3-3, EN 61000-6-2, EN 55024, EN 61000-4-2 Level 4, EN 61000-4-3 Level 3, EN 61000-4-4 Level 4, EN 61000-4-5 L-Level 3, L/N-FG Level 4, EN 61000-4-6 Level 3, EN 61000-4-8 Level 4, EN 61000-4-11, ENV 50204 Level 2, EN 61204-3
<b>Shock resistance</b>	meet IEC 60068-2-27 (15G, 11ms, 3 Axis, 6 faces, 3 times for each face)		
<b>UL / cUL</b>	UL508 listed, UL60950-1, UL1310 Class 2 Power Recognized, ISA 12.12.01 (Class 1, Division 2, Groups A, B, C and D)		
<b>TUV</b>	EN 60950-1, CB scheme		
<b>CCC</b>	GB4943, GB9254, GB17625.1		


## Block Diagrams




## Pin Assignment and Front Controls

Pin No.	Designation	Description
1	V+	Positive output terminal
2	V-	Negative output terminal
3		Ground terminal to minimise High frequency emissions
4	N	Input terminals (neutral conductor, no polarity at DC input)
5	L	Input terminals (phase conductor, no polarity at DC input)
	ON	Operation indicator LED
	LO	DC LOW indicator LED
	Vout ADJ.	Trimmer-potentiometer for Vout adjustment


## Derating Diagram




## Typ. Current Limited Curve



## Mechanical Drawings mm (inches)



## Typ. Efficiency Curve



## Installation

<b>Ventilation and cooling</b>	Normal convection All sides 25mm free space for cooling is recommended
<b>Connector size range</b>	AWG24-14 (0.2~2mm <sup>2</sup> ) flexible/solid cable, 10mm stripping at cable and recommends use copper conductors only, 60/75°C
<b>Spring terminal</b>	
<b>Screw terminal</b>	AWG26-12 (0.2~2.5mm <sup>2</sup> ) flexible/solid cable, connector can withstand torque at max 0,56Nm (5 lbs-in). 4~5 mm stripping at cable and recommends use copper conductors only, 60/75°C
<b>Max. torque for terminal</b>	
<b>Input terminals</b>	0.56Nm (5.0lb-in)
<b>Output terminals</b>	0.56Nm (5.0lb-in)
<b>General tolerances mm(in.)</b>	
<b>0.00 (0.00) ÷ 30.00 (1.18)</b>	±0.30 (0.01)
<b>30.00 (1.18) ÷ 120.00 (4.72)</b>	±0.50 (0.02)