

Description

STAINLESS STEEL TOP PLATE CASTOR, GREY RUBBER 50MM

Fixed

JF2BA050-325L



Part Number

Swivel

JP2BA050-325L




Swivel and brake

JP2BD050-325L



	Fixed	Swivel	Swivel+brake
Wheel Diameter ØD	50 mm		
Overall Height H	70 mm ±1		
Size of plate A X B	60 x 60 mm±1		
Plate hole centres a x b	45 x 45 mm±0,3		
Plate hole	6,5 mm		
Offset F ±1	\	25 mm	25 mm
Width of Tread	18 mm±0,5		
Hardness of tread	shore A ± 93		
Load capacity	40 Kg		
Weight	0,2 kg	0,24 kg	0,3 kg
Temperature	- 5 / + 50 °C		



Castor Assembly :

Pressed stainless steel -AISI 304-. Swivel on two rows of balls.
Fastening by top plate.
Total lock. Plastic pedal.

Wheel :

Wheel centre made of Grey Polypropylene.
Tread : Thermoplastic rubber, grey non marking. Plain bearing.

Features :

Low starting effort,
Bonded Rubber,
Corrosion resistant. Easy to clean.
Suited for Food industry, Hospital or Industrial Kitchen equipment.