

FEATURES

- **Sintered Bronze Material:** Provides high durability and resistance to wear, ensuring long service life.
- **Flanged Design:** Allows for easy installation and secure fitment, reducing maintenance time.
- **Dynamic Load Rating of 14 N/mm²:** Suitable for applications with moderate dynamic loads.
- **Static Load Rating of 50 N/mm²:** Capable of handling high static loads, enhancing reliability.
- **ISO 9001:2008 Certified:** Ensures quality and consistency in manufacturing processes.

RS PRO 1.5 in Plain Bearing, Sintered Bronze Flanged

RS Stock No: 518-181



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price

Product Description

This RS PRO plain bearing is designed to provide reliable performance in various industrial applications. Made from sintered bronze, it offers excellent durability and resistance to wear. The flanged design ensures easy installation and secure fitment, making it ideal for supporting rotating or sliding components.

General Specifications

Bore Size	1.5 in
Dynamic Load Rating	14 N/mm ²
Product Type	Plain Bearing
Static Load Rating	50 N/mm ²
Sub Type	Flanged

Mechanical Specifications

Material	Sintered Bronze
Outside Diameter	1.87 in
Width	2 in

Approvals

Standards/Approvals	ISO 9001:2008, UKAS 001
---------------------	-------------------------

