




FAG

KLM11749-LM11710

Tapered roller bearing

Tapered roller bearings K-Series, in inch sizes, separable, adjusted or in pairs

Technical information



Your current product variant

Tolerance class	ABMA4	Class 4 (ANSI/ABMA 19.2:2013)
Heat treatment	Standard	
Cage	Standard	Sheet steel cage, window cage, roller-guided
Quality level	Standard	
Number of rolling element rows	1	Single-row design

Main Dimensions & Performance Data

d	17.462 mm	Bore diameter
D	39.878 mm	Outside diameter
B	14.605 mm	Width, inner ring
C	10.668 mm	Width, outer ring
T	13.843 mm	Width, total
C _r	21,200 N	Basic dynamic load rating, radial
C _{0r}	20,800 N	Basic static load rating, radial
C _{ur}	2,220 N	Fatigue load limit, radial
n _G	20,100 1/min	Limiting speed
n _{gr}	12,100 1/min	Thermal speed rating
≈m	0.081 kg	Weight



Mounting dimensions

d _a max	22 mm	Maximum diameter of shaft shoulder
d _b min	24 mm	Minimum diameter of shaft shoulder
D _a min	34 mm	Minimum diameter of housing shoulder
D _b min	37 mm	Minimum diameter of housing shoulder
C _a min	3 mm	Minimum axial space
C _b min	3 mm	Minimum axial space
r _a max	1.3 mm	Maximum fillet radius of shaft
r _b max	1.3 mm	Maximum fillet radius of housing

Dimensions

r _{1, 2} min	1.3 mm	Minimum chamfer dimension of inner ring back face
r _{3, 4} min	1.3 mm	Minimum chamfer dimension of outer ring back face
a	9 mm	Distance between the apexes of the pressure cones
d ₁	29.6 mm	Guidance rib diameter of inner ring

Temperature range

T _{min}	-30 °C	Operating temperature min.
T _{max}	120 °C	Operating temperature max.

Calculation factors

e	0.29	Limiting value of Fa/Fr for the applicability of diff. Values of factors X and Y
Y	2.1	Dynamic axial load factor
Y ₀	1.15	Static axial load factor



Characteristics

-  Radial load
-  Axial load in one direction
-  Grease Lubrication
-  Oil Lubrication
-  Not sealed