



Product Compliance

For compliance documentation, visit the product page on TE.com>











|                                               |                                                                                                                                         |
|-----------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                               |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                               |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                                 |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2025 (247)<br>Candidate List Declared Against: JUN 2018 (191)<br>SVHC > Threshold:<br>Not Yet Reviewed |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                                     |
| Solder Process Capability                     | Not reviewed for solder process capability                                                                                              |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.




Compatible Parts

|                                                                                                                                                                  |                                                                                                                                                        |                                                                                                                                                  |                                                                                                                                                    |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------|
|  <p>TE Part # 1-794059-0<br/>MINI UMNL PIN L/P LF</p>                           |  <p>TE Part # 770834-3<br/>MINI UMNL SOCKET AU</p>                    |  <p>TE Part # 1-770985-0<br/>MINI UMNL PIN 26-22AWG AU LP</p> |  <p>TE Part # 1445818-1<br/>PLUG,11-7,SM INS,STD KEY</p>        |
|  <p>TE Part # 1-770835-0<br/>MINI UMNL PIN AU LF</p>                           |  <p>TE Part # 1-770902-1<br/>MINI UMNL SOK 26-22 AWG AU LF</p>       |  <p>TE Part # 1445420-2<br/>SEAL,FLANGE,SIZE 11</p>          |  <p>TE Part # 1-770904-1<br/>MINI UMNL SOK 22-18AWG AU LF</p>  |
|  <p>TE Part # 770985-1<br/>MINI UMNL PIN 26-22AWG SN LP</p>                   |  <p>TE Part # 770903-3<br/>MINI UMNL PIN 22-18 AWG AU</p>           |  <p>TE Part # 770835-3<br/>MINI UMNL PIN AU</p>             |  <p>TE Part # 770902-4<br/>MINI UMNL SOCK 26-22 AWG SN</p>    |
|  <p>TE Part # 770985-3<br/>MINI UMNL PIN 26-22AWG AU LP</p>                   |  <p>TE Part # 794058-1<br/>MINI UMNL SOK L/P</p>                    |  <p>TE Part # 770903-6<br/>MINI UMNL PIN 22-18 AWG AU</p>   |  <p>TE Part # 1-770834-1<br/>MINI UMNL SOK PHBRZ AU LF</p>    |
|  <p>TE Part # 1-2407269-2<br/>CAP, CPC, SIZE 11 RECP &amp; 13 PLUG, BLACK</p> |  <p>TE Part # 1546746-4<br/>R/A CABLE CLAMP KIT,SZ 11, MINI CPC</p> |  <p>TE Part # 1604089-2<br/>CAP,DUST,SIZE 11</p>            |  <p>TE Part # 1-770988-1<br/>MINI UMNL SOK 22-18AWG LP LF</p> |


Customers Also Bought



TE Part #1445818-1  
PLUG,11-7,SM INS,STD KEY



TE Part #EN3750-475  
TCTL-1-5/16-U




TE Part #1623804-3  
SQZ10 3R9 5% WIRE




TE Part #7-2176460-2  
SMF 7W 1M0 5% Taped



TE Part #3-644488-3  
13P MTA100 SHRD HDR F/L R/A SN



TE Part #NB-PTCO-166  
Pt100, 2.0x5.0, Class C, PTFD101C1A0



TE Part #1-2314916-0  
10P,2MM,B-B,REC,DRHZ,2.1,0.1AU,TB



TE Part #CAT-P851-T1  
PCB Power Relay: 30 amp, Monostable DC

Documents

Product Drawings

REC,11-7,FLNG MT,SM INS,STD KE

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_1445822-1\_C.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_1445822-1\_C.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_1445822-1\_C.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1-1773902-9\_CPC\_Catalog

English

1-1773902-9\_CPC\_Catalog

1-1773902-9\_CPC\_Catalog

German

1-1773902-9\_CPC\_Catalog

Japanese

AMP Circular Connectors for Commercial Signal & Power Applications Continued



English

- Product Specifications
- Application Specification

English