

## HIGH EFFICIENCY 600X600 LED PANEL 100LM/W

LD3PAN3853U



38,0 W - 3800lm - 4000K

IP40

25.000 H



CRI>80



DIMENSIONS	A	B	C
1	10	---	595












Driver compreso  
nella confezione /  
Driver included

### GENERAL INFORMATIONS

Code	LD3PAN3853U
Ean	8031453021771
Family	HIGH EFFICIENCY 600X600 LED PANEL 100LM/W
Technology	LED
Body material	Metal
Diffuser / lens material	PC
Operating temperature (° C)	-20 - +40

### PACKAGING

Packaging	BOX
Pack	5

ACCESSORIES		
	CONSTANT CURRENT LED DRIVER FOR LED PANEL	LD3PAND38
	CONSTANT CURRENT LED DRIVER FOR LED PANEL	LD3PAND42D
	CONSTANT CURRENT LED DRIVER FOR LED PANEL	MFD-1100-42-D
	SUSPENDED MOUNTING KIT	LD3PAN CAB
	UNIVERSAL CEILING MOUNTING KIT ASSEMBLY WITH SCREWS	LD2PANFRM-2
	UNIVERSAL SURFACE MOUNTING KIT	LD4PANFRM
	RECESS MOUNTING KIT WITH SPRINGS	LD3PANSPG
	UNIVERSAL RECESSED MOUNTING KIT WITH FRAME	LD3PANINK
	MULTIFUNCTIONAL EMERGENCY KIT	EMK5-90-15-A

LIGHTING DATA	
Kelvin (°)	4000
Lumen	3800
Beam (°)	90
Luminous efficacy (lm / W)	100
Color rendering (CRI)	>80
TECHNICAL FEATURES	
Power (W)	38,0
Supply voltage (V) / Max (V)	220 / 240
Power frequency (Hz)	50/60
Insulation class	2
Power factor	>0,90
Dimmer compatibility	NO

