



# SS22 THRU SS210

## 2.0 AMPS. Surface Mount Schottky Barrier Rectifiers



Voltage Range  
20 to 100 Volts  
Current  
2.0 Amperes


### Features

- ✦ For surface mounted application
- ✦ Metal to silicon rectifier, majority carrier conduction
- ✦ Low forward voltage drop
- ✦ Easy pick and place
- ✦ High surge current capability
- ✦ Plastic material used carriers Underwriters Laboratory Classification 94V-0
- ✦ Epitaxial construction
- ✦ High temperature soldering:  
260°C / 10 seconds at terminals

### Mechanical Data

- ✦ Case: Molded plastic
- ✦ Terminals: Solder plated
- ✦ Polarity: Indicated by cathode band
- ✦ Packaging: 12mm tape per EIA STD RS-481
- ✦ Weight: 0.093gram

### SMB/DO-214AA



Dimensions in inches and (millimeters)

### Maximum Ratings and Electrical Characteristics

Rating at 25°C ambient temperature unless otherwise specified.

Single phase, half wave, 60 Hz, resistive or inductive load.

For capacitive load, derate current by 20%

Type Number	Symbol	SS 22	SS 23	SS 24	SS 25	SS 26	SS 29	SS 210	Units
Maximum Recurrent Peak Reverse Voltage	$V_{RRM}$	20	30	40	50	60	90	100	V
Maximum RMS Voltage	$V_{RMS}$	14	21	28	35	42	63	70	V
Maximum DC Blocking Voltage	$V_{DC}$	20	30	40	50	60	90	100	V
Maximum Average Forward Rectified Current at $T_L$ (See Fig. 1)	$I_{(AV)}$	2.0							A
Peak Forward Surge Current, 8.3 ms Single Half Sine-wave Superimposed on Rated Load (JEDEC method)	$I_{FSM}$	50							A
Maximum Instantaneous Forward Voltage (Note 1) @ 2.0A	$V_F$	0.5		0.70		0.85		V	
Maximum DC Reverse Current @ $T_A = 25^\circ\text{C}$ at Rated DC Blocking Voltage @ $T_A = 100^\circ\text{C}$	$I_R$	0.4					0.1		mA
		20			10.0		20		
Typical Junction Capacitance (Note 3)	$C_j$	130							pF
Typical Thermal Resistance ( Note 2 )	$R_{\theta_{JL}}$	17							$^{\circ}\text{C}/\text{W}$
	$R_{\theta_{JA}}$	75							
Operating Temperature Range	$T_J$	-65 to +125			-65 to +150				$^{\circ}\text{C}$
Storage Temperature Range	$T_{STG}$	-65 to +150							

Notes: 1. Pulse Test with PW=300 usec, 1% Duty Cycle

2. Measured on P.C.Board with 0.4 x 0.4" (10 x 10mm) Copper Pad Areas.

3. Measured at 1 MHz and Applied Reverse Voltage of 4.0V D.C.

## RATINGS AND CHARACTERISTIC CURVES (SS22 THRU SS210)

FIG. 1- MAXIMUM FORWARD CURRENT DERATING CURVE




FIG. 2- MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT




FIG. 3- TYPICAL FORWARD CHARACTERISTICS




FIG. 4- TYPICAL REVERSE CHARACTERISTICS




FIG. 5- TYPICAL JUNCTION CAPACITANCE




FIG. 6- TYPICAL CAPACITANCE

