



Example image

- APPLICATION PURPOSES
- For chemicals and technical liquids
 - For industrial gases (e.g. acetylene, shielding gases)
- CHARACTERISTICS
- Silicone-free (LABS-free)

- Suitable for loose flange, in accordance with EN 1092-1, flange type 02

TECHNICAL DATA

Product material

CrNiMo steel 1.4401 (EN 10088)

- TO ORDER ADDITIONALLY
- Loose flange (to be ordered on site)
- ACCESSORIES
- Geberit flange gasket, fibre composite material PN 6

Art. no.	DN	d, ø mm	de, ø mm	di, ø mm	D cm	H cm	h cm	K cm	PN bar
These articles are suitable for the following system: Geberit Mapress Stainless Steel (silicone-free)									
36150	25	28	32	25.6	6	13.5	0.6	3.7	6
36151	32	35	40	32	7	13.5	0.6	2.7	6
36152	40	42	47	39	8	13.5	0.6	0	6
36153	50	54	59	51	9	13.5	0.8	0	6

<i>Art. no.</i>	<i>DN</i>	<i>d_e ø mm</i>	<i>d_f ø mm</i>	<i>d_i ø mm</i>	<i>D cm</i>	<i>H cm</i>	<i>h cm</i>	<i>K cm</i>	<i>PN bar</i>
36154	65	76.1	78	73.1	11	13.5	0.8	0	6
36155	80	88.9	91	84.9	12.8	13.5	1	0	6
36156	100	108	110	104	14.8	13.5	1	0	6

These articles are suitable for the following system: **Geberit Mapress Stainless Steel (FKM blue)**

36150	25	28	32	25.6	6	13.5	0.6	3.7	6
36151	32	35	40	32	7	13.5	0.6	2.7	6
36152	40	42	47	39	8	13.5	0.6	0	6
36153	50	54	59	51	9	13.5	0.8	0	6
36154	65	76.1	78	73.1	11	13.5	0.8	0	6
36155	80	88.9	91	84.9	12.8	13.5	1	0	6
36156	100	108	110	104	14.8	13.5	1	0	6

These articles are suitable for the following system: **Geberit Mapress Stainless Steel**

36150	25	28	32	25.6	6	13.5	0.6	3.7	6
--------------	----	----	----	------	---	------	-----	-----	---

Art. no.	DN	d _ø mm	d _ø mm	d _i mm	D cm	H cm	h cm	K cm	PN bar
36151	32	35	40	32	7	13.5	0.6	2.7	6
36152	40	42	47	39	8	13.5	0.6	0	6
36153	50	54	59	51	9	13.5	0.8	0	6
36154	65	76.1	78	73.1	11	13.5	0.8	0	6
36155	80	88.9	91	84.9	12.8	13.5	1	0	6
36156	100	108	110	104	14.8	13.5	1	0	6

These articles are suitable for the following system: **Geberit Mapress Therm**

36150	25	28	32	25.6	6	13.5	0.6	3.7	6
36151	32	35	40	32	7	13.5	0.6	2.7	6
36152	40	42	47	39	8	13.5	0.6	0	6
36153	50	54	59	51	9	13.5	0.8	0	6
36154	65	76.1	78	73.1	11	13.5	0.8	0	6
36155	80	88.9	91	84.9	12.8	13.5	1	0	6

Art. no.	DN	d, ø mm	de, ø mm	di, ø mm	D cm	H cm	h cm	K cm	PN bar
36156	100	108	110	104	14.8	13.5	1	0	6