

SCK-M-U-1500V-10PCS - PV string monitoring module



1084352

<https://www.phoenixcontact.com/in/products/1084352>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

SCK measuring module for monitoring photovoltaic systems, 1 x voltage measurement up to 1500 V DC, 1 x analog output (2 ... 10 V)



Commercial data

Item number	1084352
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	*****
Product key	CMMD32
GTIN	4055626822730
Weight per piece (including packing)	1,331 g
Weight per piece (excluding packing)	1,281 g
Customs tariff number	90303370
Country of origin	DE

SCK-M-U-1500V-10PCS - PV string monitoring module



1084352

<https://www.phoenixcontact.com/in/products/1084352>

Set consists of

SCK-M-U-1500V - PV string monitoring module

2903591

<https://www.phoenixcontact.com/in/products/2903591>



SCK measuring module for monitoring photovoltaic systems, 1 x voltage measurement up to 1500 V DC, 1 x analog output (2 ... 10 V)

SCK-M-U-1500V-10PCS - PV string monitoring module



1084352

<https://www.phoenixcontact.com/in/products/1084352>

Technical data

Product properties

Product type	Voltage transducer
Product family	SOLARCHECK

Insulation characteristics

Pollution degree	2
------------------	---

Electrical properties

Protective circuit	Surge protection; 33 V suppressor diode
--------------------	---

Supply

Nominal supply voltage	24 V DC -10 % ... +25 % (or via SSCK-M-I-8S-20A)
Supply voltage range	21.6 V DC ... 30 V DC
Own current consumption	8 mA (typical)
	65 mA (maximum)

Input data

Measurement

Number of inputs	1
Input voltage range	0 V DC ... 1500 V DC (CAT III)
	0 V DC ... 1000 V DC (UL)
Input resistance of voltage input	2x 20 MΩ
Connection method	Screw connection
Impulse form	DC voltage
Temperature coefficient, typical	< 0.01 %/K
Maximum transmission error	± 1 % (after additional tuning (valid for 100 - 1,500 V DC))

Output data

Signal: analog

Voltage output signal	2 V DC ... 10 V DC
Load	10 kΩ
Cable type	Twisted, shielded

Connection data

Connection method	Screw connection
Conductor cross section rigid	0.2 mm² ... 2.5 mm²
Conductor cross section flexible	0.2 mm² ... 2.5 mm²
Conductor cross section AWG	24 ... 12
Tightening torque	0.5 Nm ... 0.6 Nm

Dimensions

Width	22.5 mm
-------	---------

SCK-M-U-1500V-10PCS - PV string monitoring module



1084352

<https://www.phoenixcontact.com/in/products/1084352>

Height	102 mm
Depth	128.5 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-20 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Altitude	≤ 2000 m
Permissible humidity (operation)	≤ 95 % (non-condensing)

Approvals

CE

Certificate	CE-compliant
-------------	--------------

UL, USA/Canada

Identification	508 Listed
----------------	------------

UL, USA

Identification	1741 Recognized
----------------	-----------------

EMC data

Electromagnetic compatibility	Conformance with EMC directive
Low Voltage Directive	Conformance with Low Voltage Directive
Noise immunity	EN 61000-6-2
Note	When being exposed to interference, there may be minimal deviations.
Noise emission	EN 61000-6-4

Standards and regulations


Standards/regulations	EN 61010-1
	EN 61010-2-30

Mounting

Mounting type	DIN rail: 35 mm
	DIN rail mounting

Drawings

Block diagram



SCK-M-U-1500V-10PCS - PV string monitoring module



1084352

<https://www.phoenixcontact.com/in/products/1084352>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1084352>



UL Recognized

Approval ID: FILE E 325209



UL Listed

Approval ID: E140324



cUL Listed

Approval ID: E140324

cULus Listed

SCK-M-U-1500V-10PCS - PV string monitoring module



1084352

<https://www.phoenixcontact.com/in/products/1084352>

Classifications

ECLASS

ECLASS-11.0	27210125
ECLASS-12.0	27210125
ECLASS-13.0	27210125

ETIM

ETIM 9.0	EC002477
----------	----------

UNSPSC

UNSPSC 21.0	39121000
-------------	----------

SCK-M-U-1500V-10PCS - PV string monitoring module



1084352

<https://www.phoenixcontact.com/in/products/1084352>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	N,N-dimethylacetamide(CAS: 127-19-5)
	Lead(CAS: 7439-92-1)
SCIP	65eddd4c-01f9-4243-a00c-e58abb140c75

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420
info@phoenixcontact.co.in