

## General Information

<b>Extended Product Type:</b>	ZS6-D2-OR
<b>Product ID:</b>	1SNK506230R0000
<b>EAN:</b>	3472595062300
<b>Catalog Description:</b>	ZS6-D2-OR Screw Clamp Terminal Block - Double Deck - Orange
<b>Long Description:</b>	- Save space with double deck terminal blocks: 2 independent circuits connected in just 6 mm 0.236 in spacing, - Customize yourself the ZS6-D2 by soldering electronic components (up to 8.8 mm x 3.2 mm 0.346 x 0.125 in) in the existing linking bars punching, - Boost the performances: ZS6-D... with ES4-D2 end section is rated 1000 V DC IEC, perfectly adapted to solar applications.

## Additional Information

<b>ABB Industrial IT Suite:</b>	Control IT
<b>ATEX Certificate:</b>	1SND162004A1707
<b>Ambient Air Temperature:</b>	Operation -55 ... +110 °C Storage -55 ... +110 °C
<b>Ambient Temperature:</b>	-5 ... +40 °C
<b>BV Certificate:</b>	1SND161073A0204
<b>CB Certificate:</b>	1SND161026A0204
<b>CSA Certificate:</b>	1SND161070A0209
<b>Color:</b>	Orange
<b>Connecting Capacity Main Circuit UL/CSA:</b>	Screw Clamp / Flexible 1x 24 ... 10 AWG Screw Clamp / Flexible 2x 24 ... 14 AWG Screw Clamp / Rigid 1x 24 ... 10 AWG Screw Clamp / Rigid 2x 24 ... 14 AWG Screw Clamp / With Insulated Ferrule 1x 24 ... 12 AWG Screw Clamp / Without Insulated Ferrule 1x 24 ... 12 AWG Screw Clamp / With Twin Ferrule 2x 24 ... 14 AWG
<b>Connecting Capacity UL/CSA:</b>	Stranded 10 AWG
<b>Connecting Capacity Main Circuit:</b>	Screw Clamp / Flexible 1x 0.2 ... 6 mm <sup>2</sup> Screw Clamp / Flexible 2x 0.2 ... 2.5 mm <sup>2</sup> Screw Clamp / Rigid 1x 0.2 ... 6 mm <sup>2</sup> Screw Clamp / Rigid 2x 0.2 ... 2.5 mm <sup>2</sup> Screw Clamp / With Insulated Ferrule 1x 0.22 ... 4 mm <sup>2</sup> Screw Clamp / Without Insulated Ferrule 1x 0.22 ... 4 mm <sup>2</sup> Screw Clamp / With Twin Ferrule 2x 0.22 ... 2.5 mm <sup>2</sup>
<b>Connection Type:</b>	Screw clamp
<b>Country of Origin:</b>	France (FR)
<b>Customs Tariff Number:</b>	85369010
<b>DNV Certificate:</b>	1SND161087A0202
<b>Data Sheet, Technical Information:</b>	1SNK161014D0201
<b>Declaration of Conformity - CE:</b>	1SND225112U1001
<b>Degree of Protection:</b>	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
<b>Dielectric Test Voltage:</b>	2000 V
<b>E-nummer:</b>	2925938
<b>EAC Certificate:</b>	1SND161010A1100
<b>EAN:</b>	3472595062300
<b>ETIM 4:</b>	EC000897 - Feed-through terminal block
<b>ETIM 5:</b>	EC000897 - Feed-through terminal block
<b>ETIM 6:</b>	EC000897 - Feed-through terminal block

Environmental Information:	1SND220071E1000
Flammability According to UL94:	V0
Function:	Feed-through
Gauge Type:	A4-B3
IIT Publishing Status:	Level 0 - Information enabled
Industrial IT Certification Level:	0
Instructions and Manuals:	1SNK160027C0201
Insulation Material:	Polyamide
Invoice Description:	ZS6-D2-OR Screw Clamp Terminal Block - Double Deck - Orange
Maximum Operating Voltage UL/CSA:	Main Circuit 300 V
Minimum Order Quantity:	50 piece
Mounting on DIN Rail:	TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Number of Connections:	4
Number of Levels:	2
Object Classification Code:	X
Order Multiple:	50 piece
Package Level 1 EAN:	3472595062300
Package Level 1 Gross Weight:	0.92 kg
Package Level 1 Height:	67 mm
Package Level 1 Length:	353 mm
Package Level 1 Units:	50 piece
Package Level 1 Width:	61 mm
Package Level 2 Gross Weight:	7.860 kg
Package Level 2 Height:	200 mm
Package Level 2 Length:	400 mm
Package Level 2 Units:	400 piece
Package Level 2 Width:	300 mm
Package Level 3 Units:	19200 piece
Pollution Degree:	3
Power Loss:	2.6 W
Product Main Type:	ZS6-D2
Product Name:	Terminal Block
Product Net Depth:	65.5 mm
Product Net Height:	70.4 mm
Product Net Length:	65.5 mm
Product Net Weight:	18.4 g
Product Net Width:	6 mm
Product Packing Type:	Box
RINA Certificate:	1SND161088A0200
RMRS Certificate:	1SND161008A1101
Rated Cross-Section:	6 mm <sup>2</sup>
Rated Current (I <sub>n</sub> ):	Main Circuit 40 A
Rated Impulse Withstand Voltage (U <sub>imp</sub> ):	8000 V
Rated Short-time Withstand Current (I <sub>cw</sub> ):	for 1 s 720 A
Rated Voltage (U <sub>r</sub> ):	800 V
Recommended Screw Driver:	4 mm
Resistance to Vibrations acc. to IEC 60068-2-6:	Compliant

<b>RoHS Date:</b>	20050818
<b>RoHS Information:</b>	1SND230491F0206
<b>RoHS Status:</b>	Following EU Directive 2002/95/EC August 18, 2005 and amendment
<b>Selling Unit of Measure:</b>	piece
<b>Short Description:</b>	ZS6-D2-OR Screw Clamp Terminal Blocks
<b>Short-Circuit Current Rating (SCCR):</b>	100 kA
<b>Spacing:</b>	6 mm
<b>Sub-Function 3:</b>	2 feed-through circuits
<b>Wire Stripping Length:</b>	10.0 mm
<b>cUL Certificate:</b>	1SND161040A0206
<b>Number of Potentials:</b>	2
<b>IECEX Certificate:</b>	1SND162005A1706

