

9013FHG52J55X

Pumptrol, air compressor switch 9013FH, fixed differential, Off at 150 PSI, high hp



Main

Range of product	Pumptrol
Pressure sensor name	9013FH
Pressure sensor size	1378.95 kPa
Value of setting	Off at 150 psi
Electrical circuit type	Power circuit
Product specific application	Control small electrically driven air compressors
Quantity per set	1
Type of packing	Individual

Complementary

Pressure sensor type	Electromechanical pressure switch
Controlled fluid	Air (-0...70 °C)
Adjustable range on rising pressure	689.5...1379.0 kPa
Approximate fixed differential	275.8 kPa
Destruction pressure	1516.8 kPa
Pressure actuator	Diaphragm
Pressure switch type of operation	Regulation between 2 thresholds
Scale type	Fixed differential
Setting	Internal
Local display	Without
Contacts type and composition	2 NC, snap action, DPST-DB, Form YY
Cable entry number	2 22.35 mm cable entries with 0.84 in across flats conforming to UL 508
Electrical connection	Screw-clamp terminals, clamping capacity: 10 AWG Screw-clamp terminals, clamping capacity: 5.261 mm ²
Fluid connection type	0.25 inch NPSF internal conforming to UL 508
Short-circuit protection	20 A cartridge fuse, type gG
Materials in contact with fluid	Zinc plated steel or equivalent flange Nitrile (Buna-N) or equivalent rubber diaphragm
Material	Polypropylene: cover Noryl thermoplastic resin or equivalent: cover
Operating position	Any position
Motor power kW	1.5 KW (2 hp) at 115 V AC, 1 phase 2.2 KW (3 hp) at 115 V AC, 3 phases 2.2 KW (3 hp) at 230 V AC, 1 phase 3.7 kW (5 hp) at 230 V AC, 3 phases
Electrical durability	100000 cycles, operating rate <10 cyc/mn
Mechanical durability	300000 cycles
Terminal block type	4 terminals
Maximum operating rate	10 cyc/mn
[Ui] rated insulation voltage	575 V conforming to UL 508
Net weight	0.5 kg
Repeat accuracy	+/- 3 %
Terminals description ISO n°1	L2-T2 L1-T1
Width	70.61 mm
Height	94.23 mm

Depth	95.50 mm
Factory modification	2-way pressure release valve

Environment

Standards	UL 508 CE
Ambient air temperature for operation	-22...158 °F
Ambient air temperature for storage	-22...158 °F
Protective treatment	None
NEMA degree of protection	NEMA 1 conforming to UL 50
IP degree of protection	IP20 conforming to IEC 60529
Product certifications	CSA[RETURN]UL listed

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	25.806 cm
Package 1 Width	10.16 cm
Package 1 Length	65.548 cm
Package 1 Weight	394.625 g
Unit Type of Package 2	CAR
Number of Units in Package 2	50
Package 2 Height	22.098 cm
Package 2 Width	38.608 cm
Package 2 Length	52.832 cm
Package 2 Weight	20.598 kg

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
For all Reach Rohs enquiries contact us at	sustainability@tesensors.com

Contractual warranty

Warranty	18 months
----------	-----------