

FAG



23064-BEA-XL-K-MB1-C3

Spherical Roller Bearing

Spherical roller bearing 230...-BEA-XL-K-MB1, symmetric 2 outer ribs with rib washer

X-life

Technical information



Your current product variant

Design	BEA	with lose center lip ring
Bore type	K	Tapered, taper 1:12
Cage	MB1	Solid brass cage
Radial internal clearance	C3 (Group 3)	Internal clearance larger than CN
Relubrication feature	Standard	

Main Dimensions & Performance Data

d	320 mm	Bore diameter
D	480 mm	Outside diameter
B	121 mm	Width
C _r	2,300,000 N	Basic dynamic load rating, radial
C _{0r}	3,750,000 N	Basic static load rating, radial
C _{ur}	330,000 N	Fatigue load limit, radial
n _G	1,480 1/min	Limiting speed
n _{gr}	920 1/min	Reference speed
≈m	73.265 kg	Weight



Mounting dimensions

d _{a min}	334.6 mm	Minimum diameter shaft shoulder
D _{a max}	465.4 mm	Maximum diameter of housing shoulder
r _{a max}	3 mm	Maximum recess radius
d _{a max}	357 mm	Maximum diameter of shaft shoulder
d _{b min}	334 mm	Minimum cavity diameter of the sleeve
B _{a min}	13 mm	Minimum cavity width of the sleeve

Dimensions

r _{min}	4 mm	Minimum chamfer dimension
D ₁	433 mm	Bore diameter outer ring
d _s	9.5 mm	Diameter lubrication hole
n _s	17.7 mm	Width of lubricating groove

Temperature range

T _{min}	-30 °C	Operating temperature min.
T _{max}	200 °C	Operating temperature max.

Calculation factors

e	0.22	Limiting value of Fa/Fr for the applicability of diff. Values of factors X and Y
Y ₁	3.01	Dynamic axial load factor
Y ₂	4.48	Dynamic axial load factor
Y ₀	2.94	Static axial load factor

Additional information

H3064-HG	Adapter sleeve
AH3064G-H	Withdrawal sleeve



Characteristics

-  Radial load
-  Axial load in one direction
-  Axial load in two directions
-  Grease Lubrication
-  Oil Lubrication
-  Not sealed
-  Large bearing
-  Static angular error and misalignment
-  Dynamic angular error and misalignment