



Main

Switch application	Electrical circuit control
Range of product	DuoLine
Product or component type	Selector switch
Device short name	CM'clic

Complementary

Contacts type and composition	1 C/O
[Ie] rated operational current	20 A
[Ue] rated operational voltage	250 V AC
Control type	Toggle
Local signalling	1-2 positions
Mounting mode	Fixed
Mounting support	35 mm symmetrical DIN rail
Comb busbar distribution block compatibility	Upside: Bar'clic
9 mm pitches	2
Height	82 mm
Width	18 mm
Depth	75 mm
Electrical durability	AC-22: 30000 cycles
Connections - terminals	Staggered tunnel terminal 2 cable(s) <= 2.5 mm ² rigid without Staggered tunnel terminal 2 cable(s) <= 2.5 mm ² rigid with Staggered tunnel terminal 2 cable(s) <= 2.5 mm ² flexible without Staggered tunnel terminal 2 cable(s) <= 2.5 mm ² flexible with

Environment

Standards	EN 60669-1 EN 60947-5-1
Quality labels	NF

Contractual warranty

Period	18 months
--------	-----------