



ENGLISH

Datasheet

Stock No: 280-155

RS Pro Steel Alloy Extension Spring Kit



Product Details

Compression Only and Extension Only Kits

Compression Only, Compression spring kits each offering a different size range of springs., Kit No. 1: 320 springs, 8 each of 40 different sizes., Kit No. 2: 140 springs, 5 each of 28 different sizes., Kit No. 3: 149 springs, 5 each of 27 different sizes., Extension only, Extension spring kits each offering a different size range., Kit No. 1: 200 springs, 5 each of 40 different sizes., Kit No. 2: 142 springs, 5 each of 26 and 3 each of 4 different sizes., Kit No. 3: 135 springs, 5 each of 18 and 3 each of 15 different sizes.,

Supplied in plastic compartment box with spring sizes and box layout information

Pre-galvanised music wire



ENGLISH

Product Details


Dimensions (in.)		
Compression Springs		
Kit No. 1	Kit No. 2	Kit No. 3
L. 0.3 to 1.53	L. 1.4 to 2.75	L. 0.687 to 3.75
D. 0.105 to 0.3	D. 0.25 to 0.5	D. 0.13 to 0.615

Dimensions (in.)		
Extension Springs		
Kit No. 1	Kit No. 2	Kit No. 3
L. 0.47 to 2.0	L. 1.4 to 2.84	L. 0.687 to 4.0
D. 0.114 to 0.312	D. 0.25 to 0.5	D. 0.125 to 0.625

Spring Kits

Specifications:

Material	Steel Alloy
Spring Types	Extension
Spring Quantity	200
Maximum Length	2in
Minimum Diameter	0.114in
Minimum Length	0.47in



Extension / Zugfeder / Extensión / Traction / Trazione/ Trækfjeder / Trek / Förlängning																				
D	L	d	D	L	d	D	L	d	D	L	d	D	L	d	D	L	d			
.156	.594	.020	.156	1.187	.0124	.125	1.00	.014	.125	.750	.016	.125	1.00	.018	.135	1.125	.0124	.187	.750	.016
.114	.875	.0124	.187	2.0	.020	.125	1.25	.014	.125	1.250	.016	.125	1.25	.018	.156	1.187	.0124	.187	1.00	.016
.160	.687	.0124	.125	.750	.014	.125	1.50	.014	.125	1.50	.016	.125	1.50	.018	.156	2.00	.020	.187	1.50	.016

Extension / Zugfeder / Extensión / Traction / Trazione / Trækfjeder / Trek / Förlängning																				
D	L	d	D	L	d	D	L	d	D	L	d	D	L	d	D	L	d			
.187	.750	.018	.187	.750	.020	.250	1.25	.020	.250	1.00	.024	.250	1.00	.028	.312	1.25	.028	.312	1.75	.028
.187	1.00	.018	.187	1.25	.020	.250	1.50	.020	.250	1.50	.024	.250	1.50	.028	.312	1.50	.028	.312	2.00	.028
.187	1.50	.018	.187	1.50	.020	.250	1.75	.020	.250	1.75	.024	.250	1.75	.028						

GB

D = Outside diameter
L = Free length
d = Wire diameter

All dimensions are in inches
(to convert to mm multiply by 25.4)

Material:
pre-galvanised music wire

D

D = Außendurchmesser
L = Freie Länge
d = Drahtdurchmesser

Alle Abmessungen in Zoll
(Angaben zur Umrechnung in mm mit 25,4 multiplizieren).

Werkstoff:
Vorverzinkter Saitendraht

E

D = Diámetro externo
L = Longitud indefinida
d = Diámetro del cable

Todas las medidas vienen expresadas en pulgadas
(para convertirlas a mm, multiplique por 25,4)

Material: cable de audio pregalvanizado.

F

D = Diamètre extérieur
L = Longueur libre
d = Diamètre du fil

Toutes les dimensions sont exprimées en pouces
(pour convertir en mm, multiplier par 25,4)

Matériau: corde à piano pré-galvanisée.

I

D = Diametro esterno
L = Lunghezza normale
d = Diametro filo

Tutte le dimensioni sono in pollici
(per convertire in mm, moltiplicare per 25,4)

Materiale: filo armonico pre-galvanizzato

O

D = udvendig diameter
L = fri længde
d = tråddiameter

Alle mål er angivet i tommer
(gang med 25,4 for at omregne til mm)

Materiale: galvaniseret pianotråd.

V

D = Buitendiameter
L = Vrije lengte
d = Draaddiameter

Alle maten zijn in inches
(voor vermenigvuldigen met 25,4)

Materiaal: voorverzinkte snaar.

SE

D = Ytterdiameter
L = Fri längd
d = Tråddiameter

Alla mått anges i tum
(om du vill omvandla till mm multiplicerar du med 25,4)

Material: förgalvaniserad pianotråd.