

3NA3024 LV HRC FUSE LINK 500V S.0 80A

As of 2012-02-25

LV HRC FUSE LINK GL/GG WITH NON-INSULATED GRIP LUGS WITH FRONT INDICATOR SIZE 0, 80A, AC 500V/DC 440V




Similar to image

Technical data:		
Current / for AC / rated value	A	80
Operating class of the fuse link		gG
Size of the fallback-system / acc. to DIN EN 60269-1		NH0
Supply voltage		
• for AC / rated value	V	500
• for DC	V	440
Switching capacity current		
• in accordance with IEC 60947-2 / rated value	kA	120
• with DC / in accordance with IEC 60947-2 / rated value	kA	25
Design of an identification indicator		Front indicators
Ambient temperature		
• minimum	°C	-5
• maximum	°C	40

Certificates/approvals:			
General Product Approval	Declaration of Conformity	Test Certificates	other
<input checked="" type="checkbox"/> KEMA ROSTEST <input checked="" type="checkbox"/> VDE	Manufacturer	Manufacturer	Manufacturer

Further information:
Information- and Downloadcenter (Catalogs, Brochures,...)
<http://www.siemens.com/lowvoltage/catalogs>



last change:

Aug 26, 2011