



STRATO-THERM

TE Internal #: 50846

Closed Ring Tongue Terminal, 12 – 10 AWG, M6 Stud, 6.73 mm [.265 in] Stud Diameter, Closed Barrel, Straight, Nickel Plating, STRATO-THERM

[View on TE.com >](#)

Terminals & Splices > Ring Terminals



Ring Terminal Product Type: Closed Ring Tongue Terminal

Wire Size: 5180 – 13100 CMA

Stud Size: M6

Features

Product Type Features

Ring Terminal Product Type	Closed Ring Tongue Terminal
Stud Size	M6
Sealable	No

Wire Insulation Support Retention Type	Insulation Support
--	--------------------

Configuration Features

Number of Holes	1
-----------------	---

Electrical Characteristics

Voltage Rating	300 V
----------------	-------

Body Features

Product Weight	3.105 g
----------------	---------

Contact Features

Barrel Type	Closed
Terminal Orientation	Straight
Terminal Plating Material	Nickel

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Wire Size	5180 – 13100 CMA
Stud Diameter	6.73 mm[.265 in]
Tongue Thickness	1.07 mm[.042 in]
Product Length	32.5 mm[1.28 in]
Compatible Insulation Diameter (Max)	5.44 mm[.214 in]
Compatible Insulation Diameter Range	2.59 – 5.44 mm[.102 – .214 in]

Usage Conditions

Insulation Option	Partially Insulated
-------------------	---------------------

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Packaging Features

Packaging Quantity	500
Packaging Method	Loose Piece

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part



numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1976976-1
DIES PIDG STRATO 10 DIE SET

TE Part # 69735
PIDG STRATO 12-10 DIE SET

Also in the Series | STRATO-THERM

Crimp Wire Pins, Tabs & Ferrules(1)

Ring Terminals(85)

Splices(13)

Customers Also Bought

TE Part #2-36149-3
TERMINAL,PIDG R IR 22 6

TE Part #281709-4
PLUG HE13 IDC 90 4 P AWG 24

TE Part #1-1123722-9
3.96 EP PLUG HSG 9P(NATURAL)



TE Part #1-1123722-7
3.96 EP PLUG HSG 7P(NATURAL)

TE Part #87046-2
MOD IV RECP LP

TE Part #5102155-1
A/L UNIV HDR 10P VERT

TE Part #806157-000
202D921-4/42-0

TE Part #829103-000
342A124-25-0



Documents

Product Drawings

TERMINAL,PIDG PTFE R 12-10 1/4

English

CAD Files

Customer View Model

ENG_CVM_CVM_50846_D.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_50846_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_50846_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

STRATO-THERM Terminals & Splices for High Temperature Applications

English

Product Specifications

Application Specification

English