









CAPPED VIEW




REAR VIEW



RECOMMEND MINIMUM MOUNTING PITCH



ASSEMBLY VIEW



RECOMMEND PANEL CUT OUT

PART NUMBER	CONTACT FINISH
AXS3MP	TIN PLATED
AXS3MP-AU	GOLD PLATED

NOTE:
1. MATING CONNECTOR SHELL TO HAVE MIN 1.6 SURFACE FINISH TO ACHIEVE IP RATING OF THIS CONNECTOR.
2. BLACK MOUNTING SCREW 52500011-430 x 4 PCS TO BE SUPPLIED WITH THE CONNECTOR, MAX TORQUE 0.5Nm.
3. DUE TO 0.4mm THICK RUBBER SEAL, THE DIM WILL VARY DEPENDING ON THE SCREWS TIGHTENING IN ASSEMBLY.

3	52730035-800	AXS OVERMOLDED RUBBER FLANGE BLACK	1
2	55011499-003/903	AXS3MHV WITHOUT RUBBER FLANGE - TIN/GOLD PLATED CONTACT	1
1	52500011-430	SELF TAPPING SCREW 2.9 x 1.06mm BLACK	4
ITEM	PART NUMBER	DESCRIPTION	QTY

UNLESS OTHERWISE SPECIFIED TOLERANCE TO BE	
LINEAR	ANGULAR
X ± 0.5	X' ± 1
X.X ± 0.2	X.X' ± 30'
X.XX ± 0.1	X.XX' ± 15'
BREAK ALL SHARP EDGES AND REMOVE ALL BURRS	
DO NOT SCALE	
DIMENSIONS IN MILLIMETRES	

THIS DOCUMENT IS THE PROPERTY OF AMPHENOL AUSTRALIA PTY. LTD.
NO PART THEREOF MAY BE REPRODUCED AND USED WITHOUT THE PRIOR WRITTEN CONSENT OF THE OWNER

MATERIAL:
SEE COMPONENT

DRN: M.H
CKD: M.H

DATE: 11-11-23
DATE: 11-11-23

APP'D: P.M
SCALE: 1:1

DATE: 11-11-23
SIZE: A4

Amphenol Amphenol Australia Pty.Ltd,
22 Industry Blvd, Carrum Downs, VIC 3201

TITLE:
**AXS3MP
AXS PANEL MOUNT SERIES
CUSTOMER DRAWING**

PART No.	
SEE TABLE	
DRAWING No.	SHEET
55011499-803-2	2/2