

## C-LAB bezel, pushbutton, green

**DISCONTINUED**

### fields of application

- Measurement-control-regulation
- Electrical engineering
- Mechanical and system engineering
- Signalling systems
- Handheld terminals
- Industrial robots
- Model construction

### description

The C-LAB bezels are used for insertion into the LUMOTAST 16 pushbuttons or illuminated pushbuttons. The C-LAB bezels are fixed with the LUMOTAST 16 front rings.

### technical data

#### ➤ general

|                              |             |
|------------------------------|-------------|
| Bezel color                  | green       |
| Property of bezel / mushroom | translucent |
| Bezel shape                  | round       |
| Operating temperature, min.  | -25 °C      |
| Operating temperature, max.  | 70 °C       |
| Storage temperature, min.    | -40 °C      |
| Storage temperature, max.    | 80 °C       |
| Packaging unit               | 10 pcs.     |
| net weight                   | 0.1 g       |
| MOQ order                    | 10 pcs.     |
| RoHS compliant               | Yes         |
| REACH compliant              | Yes         |

#### direct links

- [RAFI eCatalog](#)

#### ➤ mounting diameters

|                           |         |
|---------------------------|---------|
| Outside dimension, length | 17.8 mm |
| Outside dimension, width  | 17.8 mm |
| Outside dimension, height | 2.3 mm  |

## drawings

---

### Dimensioned drawing

