

## Data sheet

**3TH4293-0BF4**



Figure similar

contactor relay, 44E, EN 50011, 4 NO + 4 NC, 1U screw terminal DC operation  
110 V DC

|                                                                         |                                                                          |
|-------------------------------------------------------------------------|--------------------------------------------------------------------------|
| product designation                                                     | Auxiliary contactor                                                      |
| product type designation                                                | 3TH4                                                                     |
| size of contactor                                                       | 0                                                                        |
| reference code according to IEC 81346-2                                 | K                                                                        |
| Substance Prohibittance (Date)                                          | 03/01/2017                                                               |
| Weight                                                                  | 0.656 kg                                                                 |
| ambient temperature during operation                                    | -25 ... +55 °C                                                           |
| type of voltage of the control supply voltage                           | DC                                                                       |
| control supply voltage at DC rated value                                | 110 V                                                                    |
| number of NC contacts for auxiliary contacts                            | 3                                                                        |
| • delayed switching                                                     | 0                                                                        |
| • lagging switching                                                     | 1                                                                        |
| • make-before-break switching                                           | 1                                                                        |
| number of NO contacts for auxiliary contacts                            | 3                                                                        |
| • delayed switching                                                     | 0                                                                        |
| • leading contact                                                       | 1                                                                        |
| • make-before-break switching                                           | 1                                                                        |
| number of CO contacts for auxiliary contacts                            | 0                                                                        |
| identification number and letter for switching elements                 | 44 E, 1U                                                                 |
| operational current at AC-15                                            |                                                                          |
| • at 230 V rated value                                                  | 10 A                                                                     |
| • at 400 V rated value                                                  | 6 A                                                                      |
| fastening method                                                        | screw and snap-on mounting onto 35 mm DIN rail according to DIN EN 50022 |
| height                                                                  | 78 mm                                                                    |
| width                                                                   | 45 mm                                                                    |
| depth                                                                   | 135 mm                                                                   |
| type of electrical connection for auxiliary and control circuit         | screw-type terminals                                                     |
| Safety related data                                                     |                                                                          |
| product function positively driven operation according to IEC 60947-5-1 | No                                                                       |
| B10 value with high demand rate according to SN 31920                   | 1 000 000; With 0.3 x Ie                                                 |
| IEC 61508                                                               |                                                                          |
| T1 value                                                                |                                                                          |
| • for proof test interval or service life according to IEC 61508        | 20 a                                                                     |
| Electrical Safety                                                       |                                                                          |
| protection class IP on the front according to IEC 60529                 | IP00; IP20 with screws tightened, even for contacts not in use           |
| Approvals Certificates                                                  |                                                                          |
| General Product Approval                                                | Functional Saftey                                                        |



[Type Examination Certificate](#)

| Test Certificates | other |
|-------------------|-------|
|-------------------|-------|

[Type Test Certificates/Test Report](#)

[Miscellaneous](#)

[Special Test Certificate](#)

[Miscellaneous](#)



[Confirmation](#)

| Railway | Environment |
|---------|-------------|
|---------|-------------|

[Special Test Certificate](#)

[Environmental Conformations](#)

#### Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3TH4293-0BF4>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3TH4293-0BF4>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3TH4293-0BF4>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)



[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3TH4293-0BF4&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3TH4293-0BF4&lang=en)

Characteristic: Tripping characteristics, I<sup>2</sup>t, Let-through current

<https://support.industry.siemens.com/cs/ww/en/ps/3TH4293-0BF4/char>

Further characteristics (e.g. electrical endurance, switching frequency)

<http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3TH4293-0BF4&objecttype=14&gridview=view1>



last modified:

4/2/2025 