

# Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2015 with regard to energy labelling of light sources

**Supplier's name or trade mark:** RS PRO

**Supplier's address:** RS PRO Compliance, Birchington Road, Corby, Northamptonshire, NN17 9RS, United Kingdom

**Model identifier:** 777-7971

## Type of light source:

Lighting technology used:	LED	Non-directional or directional:	DLS
Light source cap-type (or other electric interface)	na		
Mains or non-mains:	NMLS	Connected light source (CLS):	No
Colour-tuneable light source:	No	Envelope:	-
High luminance light source:	No		
Anti-glare shield:	No	Dimmable:	No

## Product parameters

Parameter	Value	Parameter	Value
-----------	-------	-----------	-------

### General product parameters:

Energy consumption in on-mode (kWh/1000 h), rounded up to the nearest integer	9	Energy efficiency class	E
Useful luminous flux ( $\phi_{\text{use}}$ ), indicating if it refers to the flux in a sphere (360°), in a wide cone (120°) or in a narrow cone (90°)	1 100 in Wide cone (120°)	Correlated colour temperature, rounded to the nearest 100 K, or the range of correlated colour temperatures, rounded to the nearest 100 K, that can be set	5 504
On-mode power ( $P_{\text{on}}$ ), expressed in W	9,0	Standby power ( $P_{\text{sb}}$ ), expressed in W and rounded to the second decimal	0,00
Networked standby power ( $P_{\text{net}}$ ) for CLS, expressed in W and rounded to the second decimal	-	Colour rendering index, rounded to the nearest integer, or the range of CRI-values that can be set	82
Outer dimensions without separate control gear, light-	Height	Spectral power distribution in the range 250 nm to 800 nm, at full-load	See image in last page
	Width		
	Depth		


ing control parts and non-lighting control parts, if any (millimetre)				
Claim of equivalent power <sup>(a)</sup>	-	If yes, equivalent power (W)	-	
		Chromaticity coordinates (x and y)	0,328 0,342	
<b>Parameters for directional light sources:</b>				
Peak luminous intensity (cd)	423	Beam angle in degrees, or the range of beam angles that can be set	120	
<b>Parameters for LED and OLED light sources:</b>				
R9 colour rendering index value	1	Survival factor	1,00	
the lumen maintenance factor	1,00			

(a) '-': not applicable;

(b) '-': not applicable;

# Light intensity distribution record of one lamp at initial measurement

## LUMINOUS INTENSITY DISTRIBUTION DIAGRAM



Model placed on the Union market from 14/04/2025.



**EPREL registration number:** 2329138

<https://eprel.ec.europa.eu/qr/2329138>

**Supplier:** RS Components (Manufacturer)

**Website:** [de.rs-online.com/web/](https://de.rs-online.com/web/)

**Customer care service:**

**Name:** RS PRO Compliance

**Website:** [uk.rs-online.com](https://uk.rs-online.com)

**Email:** [RSPROcompliance@rs.rsgroup.com](mailto:RSPROcompliance@rs.rsgroup.com)

**Phone:** 01536405069

**Address:**

Birchington Road, Corby, Northamptonshire, NN17 9RS, United Kingdom