

Product datasheet

Specifications



Miniature circuit-breaker, Acti9 iC60N, 3P+N, 32 A, C curve, 6000 A (IEC 60898-1), 10 kA (IEC 60947-2)

A9F04732

Main

| | |
|---------------------------|--|
| Device application | Distribution |
| Range | Acti 9 |
| Product name | Acti9 iC60 |
| Product or component type | Miniature circuit-breaker |
| Device short name | IC60N |
| Poles description | 3P + N |
| Number of protected poles | 3 |
| Neutral position | Left |
| [In] rated current | 32 A |
| Network type | DC AC |
| Trip unit technology | Thermal-magnetic |
| Curve code | C |
| Breaking capacity | 6000 A Icn at 400 V AC 50/60 Hz conforming to EN/IEC 60898-1 36 kA Icu at 12...60 V AC 50/60 Hz conforming to EN/IEC 60947-2 10 kA Icu at 380...415 V AC 50/60 Hz conforming to EN/IEC 60947-2 20 kA Icu at 220...240 V AC 50/60 Hz conforming to EN/IEC 60947-2 6 kA Icu at 440 V AC 50/60 Hz conforming to EN/IEC 60947-2 36 kA Icu at 100...133 V AC 50/60 Hz conforming to EN/IEC 60947-2 |
| Utilisation category | Category A conforming to EN 60898-1 Category A conforming to IEC 60898-1 |
| Suitability for isolation | Yes conforming to EN 60898-1 Yes conforming to EN 60947-2 Yes conforming to IEC 60898-1 Yes conforming to IEC 60947-2 |
| Standards | EN 60947-2 IEC 60947-2 EN 60898-1 IEC 60898-1 |

Complementary

| | |
|---------------------------------------|--|
| Network frequency | 50/60 Hz |
| Magnetic tripping limit | 8 x In +/- 20 % |
| [Ics] rated service breaking capacity | 15 kA 75 % conforming to EN 60947-2 - 220...240 V AC 50/60 Hz 7.5 kA 75 % conforming to EN 60947-2 - 380...415 V AC 50/60 Hz 4.5 kA 75 % conforming to EN 60947-2 - 440 V AC 50/60 Hz 15 kA 75 % conforming to IEC 60947-2 - 220...240 V AC 50/60 Hz 7.5 kA 75 % conforming to IEC 60947-2 - 380...415 V AC 50/60 Hz 4.5 kA 75 % conforming to IEC 60947-2 - 440 V AC 50/60 Hz 27 kA 75 % conforming to IEC 60947-2 - 12...133 V AC 50/60 Hz |

27 kA 75 % conforming to EN 60947-2 - 12...133 V AC 50/60 Hz
 6000 A 100 % conforming to EN 60898-1 - 400 V AC 50/60 Hz
 6000 A 100 % conforming to IEC 60898-1 - 400 V AC 50/60 Hz

| | |
|---|---|
| Limitation class | 3 conforming to EN 60898-1 3 conforming to IEC 60898-1 |
| [Ui] rated insulation voltage | 500 V AC 50/60 Hz conforming to EN 60947-2 500 V AC 50/60 Hz conforming to IEC 60947-2 |
| [Uimp] rated impulse withstand voltage | 6 kV conforming to EN 60947-2 6 kV conforming to IEC 60947-2 |
| Contact position indicator | Yes |
| Control type | Toggle |
| Local signalling | Trip indicator |
| Mounting support | DIN rail |
| 9 mm pitches | 8 |
| Height | 91 mm |
| Width | 72 mm |
| Depth | 78.5 mm |
| Product weight | 0.5 kg |
| Colour | White |
| Mechanical durability | 20000 cycles |
| Electrical durability | 10000 cycles |
| Connections - terminals | Double terminal (top or bottom) 1...35 mm ² rigid Double terminal (top or bottom) 1...25 mm ² flexible |
| Wire stripping length | 14 mm for top or bottom connection |
| Tightening torque | 3.5 N.m top or bottom |
| Earth-leakage protection | Separate block |

Environment

| | |
|--|---|
| IP degree of protection | IP20 conforming to IEC 60529 IP20 conforming to EN 60529 |
| Pollution degree | 3 |
| Overvoltage category | IV |
| Tropicalisation | 2 |
| Relative humidity | 95 % at 55 °C |
| Ambient air temperature for operation | -35...70 °C |
| Ambient air temperature for storage | -40...85 °C |

Packing Units

| | |
|-------------------------------------|--------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Weight | 508 g |
| Package 1 Height | 7.5 cm |
| Package 1 width | 7.2 cm |
| Package 1 Length | 9.5 cm |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 3 |

| | |
|------------------------------|-----------|
| Package 2 Weight | 1.541 kg |
| Package 2 Height | 8.5 cm |
| Package 2 width | 9.8 cm |
| Package 2 Length | 22.5 cm |
| Unit Type of Package 3 | S03 |
| Number of Units in Package 3 | 33 |
| Package 3 Weight | 17.438 kg |
| Package 3 Height | 30 cm |
| Package 3 width | 30 cm |
| Package 3 Length | 40 cm |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|