



Product: [74001NH](#)

DataTuff® 5E, 4PR #24 Sol BC, PO ins, SF/UTP, LSNH Jkt, AWM 21286

Product Description

DataTuff® 5E, 4 Pair AWG 24 Bare Copper - Solid, Polyethylene insulation, SF/UTP - Overall Braid + Foil shielding, LSZH / FRNC jacket , AWM 21286

Technical Specifications

Product Overview

Suitable Applications:	Cat5e, harsh environment, IIoT, factory or process automation, video, audio, data communication, etc.
------------------------	---

Construction Details

Conductor

Size	Stranding	Material	No. of Pairs	No. of Elements
24 AWG	Solid	BC - Bare Copper	4	8

Insulation

Material	Nom. Insulation Diameter	Color Code
PE - Polyethylene	1.1 mm (0.043 in)	White/Blue & Blue, White/Orange & Orange, White/Green & Green, White/Brown & Brown

Cable Core

Description
4 pairs twisted to cable core covered with a polyester foil

Outer Shield

Shield Type	Material	Coverage
Tape	Bi-Laminate (Alum+Poly)	
Braid	Tinned Copper (TC)	80%

Table Notes:	Aluminum outside
--------------	------------------

Outer Jacket

Material	Nom. Diameter
LSZH - Low Smoke Zero Halogen (Flame Retardant)	6.8 mm (0.27 in)

Table Notes:	Black similar RAL 9005 , Green similar RAL 6024 , Blue similar RAL 5015 , Light-Blue similar RAL 5012 , Pink similar RAL 4010 , Ultramarine blue similar RAL5002
Overall Cable Diameter (Nominal):	6.8 mm (0.27 in)

Electrical Characteristics

Electricals

Max. Conductor DCR	Max. Mutual Capacitance	Max. Capacitance Unbalance	Nom. Characteristic Impedance
93.8 Ohm/km	56 pF/m (17 pF/ft)	160 pF/100m	100 Ohm

Delay

Max. Delay Skew	Nom. Velocity of Prop.
40 ns/100m	60%

High Frequency

Frequency [MHz]	Max. Insertion Loss (Attenuation) [dB/100m]	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]
1	2.1	65.3	62.3	63.2	60.2	64	61	20
4	4.0	56.3	53.3	52.32	49.3	52	49	23
10	6.3	50.3	47.3	44	41	44	41	25
16	8.0	47.2	44.2	39.2	36.2	39.9	36.9	25
20	9.0	45.8	42.8	36.8	33.8	38	35	25
31.25	11.4	42.9	39.9	31.5	28.5	34.1	31.5	23.6
62.5	16.5	38.4	35.4	21.9	18.9	28.1	25.1	21.5
100	21.3	35.3	32.3	14	11	24	21	20.1

Voltage

Voltage Rating
450 V DC and 300 V AC

Mechanical Characteristics

Temperature

Operating	Installation	Storage
-40°C to +80°C	-5°C To +50°C	-40°C To +80°C

Bend Radius

Stationary Min.	Installation Min.
35 mm (1.4 in)	70 mm

Max. Pull Tension:	80 N (18 lbf)
--------------------	---------------

Standards and Compliance

Environmental Suitability:	Indoor - Euroclass Eca, Sunlight Resistance, Oil Resistance
Flammability / Reaction to Fire:	IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
IEEE Compliance:	PoE: IEEE 802.3bt Type 1, Type 2, Type 3
Data Category:	Category 5e
TIA/EIA Compliance:	ANSI/TIA 568.2-D
ISO/IEC Compliance:	ISO/IEC 11801-1
CENELEC Compliance:	EN 50173-1
European Halogen Free Standards:	IEC 62821-1 Halogen Free Compliance = Yes, IEC 60754-1 - Halogen Amount = Zero, IEC 60754-2 - Halogen Acid Gas Amount - Max. Conductivity = 2.5 µS/mm, IEC 60754-2 - Halogen Acid Gas Amount - Min. pH = 4.3
European Directive Compliance:	EU CE Mark
UK Regulation Compliance:	UKCA Mark

History

Update and Revision:	Revision Number: 0.260 Revision Date: 04-29-2024
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	EAN
74001NH.01B100	Black	Flat Box	100 m	8719605012999
74001NH.01305	Black	Reel	305 m	8719605012975
74001NH.01500	Black	Reel	500 m	8719605012982
74001NH.04500	Blue	Reel	500 m	8719605173737
74001NH.02500	Green	Reel	500 m	8719605169228
74001NH.06B100	Light Blue	Flat Box	100 m	8719605181688
74001NH.06500	Light Blue	Reel	500 m	8719605175649
74001NH.07500	Pink	Reel	500 m	8719605175656

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.