

USB Portable SSD (Element)

20Gbps

Specifications

Capacity

- 1TB/ 2TB/ 4TB

Interface

- 20Gb Type-C (USB 3.2 Gen 2x2)

Speed Mode

- 20Gbps
- 10Gbps
- 5Gbps

Performance (up to)¹

- Burst read: 2,000 MB/s
- Burst write: 2,000 MB/s

Compatibility

- Mac OS (v.10.14.x +)
- Windows 11/10
- Linux (v. 2.6.x +)
- Chrome OS™
- Android™
- iOS/iPadOS® (v.13+)
- Gaming Consoles

Mechanical form factor

- 69.8 mm x 45 mm x 8 mm
- Color: Black/ Rose gold
- Weights: 45g

Accessories

- 20 Gbps USB-C to USB-C & USB-A hybrid cable
- Metal plates x2

Power consumption

- Active: <5.8 W
- Idle: <0.7 W

Environment

- Operating temperature: 0–60 °C
- Storage temperature: -20–85 °C

RoHS compliant

Warranty

- 5-year limited warranty³

Specification notes:

1. Performance claims
 - a. Actual performance may vary based on the hardware, software, and overall system configuration.
 - b. Sequential performance is measured with 128 KB transfer size, QD 32 and 4 KB alignment with Iometer.
 - c. Random performance is sustained performance measured with 4K/8K transfer size, QD 32 and 4 KB alignment with Iometer.
 - d. Performance test platform: CPU: Intel Core i7 4770K; motherboard: ASUS Z87-DELUXE; chipset: Intel Z87 Express; OS: Windows 8.1 Pro x64.
2. Endurance claims
 - a. DWPD stands for Drive Writes Per Day. TBW = DWPD * capacity * warranty * 365 / 1000.
 - b. Access patterns used for random workload during endurance testing is compliant with the JESD219 standard.
3. Limited warranty details: please refer to limited warranty policy and warranty terms.

Table of Contents

Specifications	1
Product Datasheet	3
1. Order Information.....	3
2. Part Number Decoder.....	3
3. Performance Information	4
4. Detailed Specifications	4
4.1 Environment Specification.....	4
4.2 Power Consumption.....	4
5. Physical Dimension Diagram.....	5
6. Compliance.....	5
Legal Information.....	6
Limited Warranty Policy	6
Warranty Terms	6
Disclaimer of liability.....	7
Copyright notice	7
Contact information	7
Revision History	8

Product Datasheet

1. Order Information

The following table lists the standard part numbers for Exascend Element portable SSD series. For customization and design service inquiries, including – but not limited to – custom operating temperature, capacity, over-provisioning, endurance, performance, and power, please contact your Exascend account manager or send us an email at sales@exascend.us.

Table 1: USB 20Gbps Element portable SSD product list

PART NUMBER	CAPACITY	FLASH TYPE	Color
EXU2S3M01TP0B	1TB	3D TLC	Black
EXU2S3M02TP0B	2TB	3D TLC	Black
EXU2S3M04TP0B	4TB	3D TLC	Black
EXU2S3M01TP0R	1TB	3D TLC	Rose Gold
EXU2S3M02TP0R	2TB	3D TLC	Rose Gold
EXU2S3M04TP0R	4TB	3D TLC	Rose Gold

2. Part Number Decoder

1	2	3	4	5	6	7
EX	U2	S3	M	**T	P0	B

- EX: Exascend
- U2: Drive Interface USB 20Gbps
- S3: SSD Controller SMI 2320
- M :Series Type Element
M= Element
- **T: Capacity
01T= 1024GB
02T= 2048GB
04T= 4096GB
- P0: Portable SSD
- B: Color
B= Black/ R= Rose Gold

3. Performance Information

Table 2: USB 20Gbps Element portable SSD performance

PART NUMBER	Flash	Capacity	Max Burst Read (MB/s)	Max Burst Write (MB/s)
EXU2S3M01TP0B	TLC	1TB	2000	2000
EXU2S3M02TP0B	TCL	2TB	2000	2000
EXU2S3M04TP0B	TLC	4TB	2000	2000
EXU2S3M01TP0R	TLC	1TB	2000	2000
EXU2S3M02TP0R	TCL	2TB	2000	2000
EXU2S3M04TP0R	TLC	4TB	2000	2000

4. Detailed Specifications

4.1 Environment Specification

Table 3: Environmental specification table

PARAMETER	VALUE
Operating temperature	0–60 °C
Storage temperature	-20–85 °C
Power supply voltage range	USB: 5V ± 5%
Humidity (non-condensing)	5–95% (Operating)

4.2 Power Consumption

Table 4: power consumption table

PARAMETER	VALUE	UNIT
Active power (Avg.)	<5.8	W
Idle mode power (Avg.)	<0.7	W

5. Physical Dimension Diagram

Figure 1: physical dimension diagram




Table 5: Physical dimensions

PHYSICAL DIMENSIONS	VALUE	UNIT
Length	69.8	mm
Width	45	mm
Thickness	8	mm

6. Compliance

Exascend portable SSD complies with the following specifications:

- FCC
- CE
- RoHS

Legal Information

Limited Warranty Policy

Exascend, Inc. ("Exascend") warrants that Exascend's product, in its original sealed packaging, will be free from defects in materials and workmanship. Subject to the conditions and limitations set forth below, Exascend will either repair or replace any part of its products that prove defective by reason of improper workmanship or materials. This warranty is non-transferable and valid only for the original purchaser of the Exascend products, except where prohibited by law. The original sales receipt or invoice, or a copy thereof, is required to establish the purchase date and original purchaser.

1. This warranty supersedes all other warranties and representations, whether oral or written, between you and Exascend. Exascend makes no other warranties, including any warranty of merchantability or fitness for a particular purpose, whether expressly or implied.
2. All warranties, whether express or implied, are limited to the periods of time set forth below. Some states and jurisdictions do not allow such exclusion of implied warranties, limitations or warranty period, so above restrictions may not apply to you.
3. Exascend may acknowledge or read and save the data and information (collectively, "Information") stored in the product during after-services. Exascend hereby agrees that Exascend will not disclose any Information to any third parties, except Exascend's employees, who may need to access the Information, with or without your prior written consent.

Warranty Terms

Exascend offers five (5) years limited warranty for portable SSD.

This Limited Warranty will not apply to, and Exascend will have no liability or obligation with respect to, problems or damage resulting from any of the following: (i) accident, modification, neglect, abuse, careless or incorrect handling, misuse or improper operation, disassembly, misapplication or use in unusual physical environments or under operating conditions not approved by Exascend (including, but not limited to, use of the Product with an improper voltage supply); (ii) normal wear and tear; (iii) removal of label(s) or sticker(s) provided on or with the Product (including all warranty or quality-control stickers, product serial or electronic numbers); (iv) problems relating to or residing in non-Exascend hardware, software or other items with which the Product is used; (v) use in an environment, in a manner or for a purpose for which the Product was not designed or not in accordance with Exascend's published documentation; (vi) installation, modification, alteration or repair by anyone other than Exascend or its authorized representatives; (vii) problems that do not relate to materials or workmanship or that have an insignificant impairment on the use or operation of the Product; or (viii) problems related to consumables; (ix) Product purchased "AS-IS" or "with known faults, defects or problems."

Disclaimer of liability

Exascend, Inc. reserves the right to make changes to specifications and product descriptions such as but not limited to numbers, parameters and other technical information contained herein without notice. Please contact Exascend, Inc. to obtain the latest specifications. Exascend, Inc. grants no warranty with respect to this datasheet, explicit or implied, and is not liable for direct or indirect damages. Some states do not grant the exclusion of incidental damages and as such this statement may not be valid in such states. The provisions of the datasheet do not convey to the purchaser of the device any license under any patent right or other intellectual property right of Exascend, Inc.

Customers must not use Exascend products in applications where a device failure or malfunction may cause personal injury or death, e.g., in life support systems or devices.

Exascend shall not be liable for any loss, injury or damage caused by use of the products in any of the following applications:

- Medical-related devices, life support, medical measurement devices, etc.
- Control devices for trains, ships, mass transportation systems or automotive vehicles, etc.
- Specific applications including military/defense-related equipment, aerospace, nuclear facility control systems, etc.
- Safety systems for disaster prevention/crime prevention, etc.

Copyright notice

Copyright © 2022 Exascend, Inc. All rights reserved. Information contained in this document, including but not limited to any instructions, descriptions, and product specifications, is considered proprietary and confidential to Exascend, Inc. and shall not be modified, used, copied, reproduced or disclosed in whole or in part, in any form or by any means, electronic or mechanical, for any purpose, without the written consent of Exascend, Inc.

Contact information

Exascend Taiwan Office

Address: Room 1, 6F, No. 288, Sec. 6, Civic Blvd., Xinyi Dist., Taipei City 110, Taiwan.

General Support: +886-2-2726-6500

Fax: +886-2-2726-6126

Email: sales@exascend.us

Revision History

REVISION	DESCRIPTION	DATE
001	First released	Dec., 2023
002	Update Power Consumption	Apr., 2024
003	Remove Data Recovery Description	Aug., 2024
004	Update cable description	Aug., 2024