




## **Dimensions: [mm]**












## **Product Marking:**

Marking	90N (Inductance Code)
Marking - Date Code	T+Year/Month/Day

## **Recommended Land Pattern: [mm]**



# Schematic:



# **Electrical Properties:**

Properties	Test conditions		Value	Unit	Tol.
Inductance	1 MHz	L	90	nH	±20%
Q-Factor	100 MHz	Q	226		typ.
DC Resistance	@ 20 °C	R <sub>DC</sub>	1.21	1.21 mΩ	
Rated Current	$\Delta T = 40 \text{ K}$	I <sub>R</sub>	30	А	max.
Self Resonant Frequency		f <sub>res</sub>	359	MHz	typ.

## **General Information:**

It is recommended that the temperature of the component does not exceed +125°C under worst case conditions

Ambient Temperature (refering to $\mathbf{I}_{\mathrm{R}}$ )	-40 °C up to +110 °C
Operating Temperature	-40 °C up to +125 °C
Storage Temperature (in original packaging)	-40 °C up to +85 °C

Test conditions of Electrical Properties: +20°C, 33% RH if not specified differently

Würth	Elektronik	eiSos	GmbH	&	Co.	KG
FMC 8	Inductive	Solution	ons			

Max-Eyth-Str. 1 74638 Waldenburg Germany Tel. +49 (0) 79 42 945 - 0

www.we-online.com eiSos@we-online.com



					0.00	
1	CREATED	CHECKED	GENERAL TOLERANCE	PROJECTION METHOD		Т
	KaS	JoMa	DIN ISO 2768-1m	METHOD	<del></del>	
ı					i	

WE-ACHC High current air coil

# **Typical Inductance vs. Frequency Characteristics: Q-Factor vs. Frequency:** 10000 280 240 1000 200 Inductance [nH] Q-factor 160 120 10 80 40 0 10 100 1000 10000 100 10 1000 Frequency [MHz] Frequency [MHz] GENERAL TOLERANCE Würth Elektronik eiSos GmbH & Co. KG CREATED CHECKED **EMC & Inductive Solutions** KaS JoMa DIN ISO 2768-1m Max-Eyth-Str. 1 74638 Waldenburg **WE-ACHC High current air coil** Tel. +49 (0) 79 42 945 - 0

**WÜRTH ELEKTRONİK** 

www.we-online.com

eiSos@we-online.com

ORDER CODE

DATE (YYYY-MM-DD)

2017-01-26

001.000

Valid

1212

7449152090


BUSINESS UNIT


eiSos


PAGE


2/6


## Packaging Specification - Tape and Reel: [mm]












		A	В	C	D	N	W1	W2	W3	W3
Tolerance		± 2,0	min.	min.	min.	± 2,0	+ 2	max.	min.	max.
Tape width	24mm	330,00	1,50	12,80	20,20	60,00	24,40	30,40	23,90	27,40

## Packaging is referred to the international standard IEC 60286 -3:2007

		A0	B0	W	T	T1	T2	K0	P0	P1	P2	D0	D1	E1	E2	F	Tape Type 2a	VPE / packaging unit
tolerance		$\pm 0,1$	±0,1	±0,1	typ.	max.	typ.	±0,15	$\pm 0,1$	±0,1	±0,1	+0,1/-0,0	min.	±0,1	min.	$\pm 0,1$		pcs.
size	1212	12.50	12.50	24.00	0.50	0.10	11.20	10.70	4.00	16.00	2.00	1.50	1.50	1.75	22.25	11.50	Polystyrene	300



Pull-of force 24 mm 0,1 N - 1,3 N Tape width

CREATED Würth Elektronik eiSos GmbH & Co. KG EMC & Inductive Solutions KaS Max-Eyth-Str. 1 74638 Waldenburg Tel. +49 (0) 79 42 945 - 0 www.we-online.com eiSos@we-online.com

WE-ACHC High current air coil

CHECKED

JoMa

ORDER CODE

7449152090 DATE (YYYY-MM-DD) REVISION STATUS


GENERAL TOLERANCE

DIN ISO 2768-1m

BUSINESS UNIT PAGE 001.000 2017-01-26 Valid eiSos 3/6 1212

**WÜRTH ELEKTRONİK** 

# **Classification Reflow Profile for SMT components:**



## **Classification Reflow Soldering Profile:**

Profile Feature		Value
Preheat Temperature Min	T <sub>s min</sub>	150 °C
Preheat Temperature Max	T <sub>s max</sub>	200 °C
Preheat Time $t_s$ from $T_{s min}$ to $T_{s max}$	t <sub>s</sub>	60 - 120 seconds
Ramp-up Rate (T <sub>L</sub> to T <sub>P</sub> )		3 °C/ second max.
Liquidous Temperature	T <sub>L</sub>	217 °C
Time $t_L$ maintained above $T_L$	t <sub>L</sub>	60 - 150 seconds
Peak package body temperature	T <sub>p</sub>	see table below
Time within 5°C of actual peak temperaure	t <sub>p</sub>	20 - 30 seconds
Ramp-down Rate (T <sub>L</sub> to T <sub>P</sub> )		6 °C/ second max.
Time 25°C to peak temperature		8 minutes max.

refer to IPC/ JEDEC J-STD-020E

# **Package Classification Reflow Temperature:**

Properties	Volume mm³ <350	Volume mm <sup>3</sup> 350-2000	Volume mm³ >2000
PB-Free Assembly   Package Thickness < 1.6 mm	260 °C	260 °C	260 °C
PB-Free Assembly   Package Thickness 1.6 mm - 2.5 mm	260 °C	250 °C	245 °C
PB-Free Assembly I Package Thickness ≥ 2.5 mm	250 °C	245 °C	245 °C

refer to IPC/ JEDEC J-STD-020E

г			ī			i			1	
	Würth Elektronik eiSos GmbH & Co. KG		CREATED	CHECKED		GENERAL TOLERANCE		PROJECTION METHOD		
	EMC & Inductive Solutions		KaS	JoMa		DIN ISO 2768-1m		METHOD	<del>-</del>	
									$\neg \varphi$	
	Max-Eyth-Str. 1		DESCRIPTION							
	74638 Waldenburg									
	Germany		WE-ACH	C High ci	urrent	air coil				
	Tel. +49 (0) 79 42 945 - 0			<b>3</b>						
							ORDER CODE			
	www.we-online.com						74491	E2000	1	
	eiSos@we-online.com						<i>  14</i> 431	<b>32030</b>	•	
			SIZE	REVISION	STATUS		DATE (YYYY-MM-DD	)	BUSINESS UNIT	PAGE
			1010	004 000	17-11-1		0017.01.00		-10	4/0
		WÜRTH ELEKTRONIK	1212	001.000	Valid		2017-01-26		eiSos	4/6
L										

## **Cautions and Warnings:**

# The following conditions apply to all goods within the product series of WE-ACHC of Würth Elektronik eiSos GmbH & Co. KG:

#### General:

All recommendations according to the general technical specifications of the data sheet have to be complied with.

The usage and operation of the product within ambient conditions, which probably alloy or harm the wire isolation, has to be avoided.

If the product is potted in customer applications, the potting material might shrink during and after hardening. The product is exposed to the pressure of the potting material with the effect that the core, wire and termination is possibly damaged by this pressure and so the electrical as well as the mechanical characteristics are endangered to be affected. After the potting material is cured, the core, wire and termination of the product have to be checked if any reduced electrical or mechanical functions or destructions have occurred.

The responsibility for the applicability of customer specific products and use in a particular customer design is always within the authority of the customer. All technical specifications for standard products do also apply to customer specific products.

Cleaning agents that are used to clean the customer application might damage or change the characteristics of the component, body, pins or termination.


Direct mechanical impact to the product shall be prevented as the core material could flake or in the worst case it could break.

## **Product specific:**

Follow all instructions mentioned in the data sheet, especially:

- The soldering profile has to be complied with according to the technical reflow soldering specification, otherwise this will void the
  warranty.
- All products shall be used before the end of the period of 12 months based on the product date code, if not a 100% solderability can't
  be ensured
- Violation of the technical product specifications such as exceeding the nominal rated current will void the warranty.
- Strong forces might have the effect to damage the coplanarity of the electrical connection (pins), will restrain the soldering and void the
  warranty
- Please notice that the recommended thickness of the soldering paste is 120 μm.

The general and product specific cautions comply with the state of the scientific and technical knowledge and are believed to be accurate and reliable; however, no responsibility is assumed for inaccuracies or incompleteness.



## **Important Notes**

# The following conditions apply to all goods within the product range of Würth Elektronik eiSos GmbH & Co. KG:

### 1. General Customer Responsibility

Some goods within the product range of Würth Elektronik eiSos GmbH & Co. KG contain statements regarding general suitability for certain application areas. These statements about suitability are based on our knowledge and experience of typical requirements concerning the areas, serve as general guidance and cannot be estimated as binding statements about the suitability for a customer application. The responsibility for the applicability and use in a particular customer design is always solely within the authority of the customer. Due to this fact it is up to the customer to evaluate, where appropriate to investigate and decide whether the device with the specific product characteristics described in the product specification is valid and suitable for the respective customer application or not.

## 2. Customer Responsibility related to Specific, in particular Safety-Relevant Applications

It has to be clearly pointed out that the possibility of a malfunction of electronic components or failure before the end of the usual lifetime cannot be completely eliminated in the current state of the art, even if the products are operated within the range of the specifications. In certain customer applications requiring a very high level of safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health it must be ensured by most advanced technological aid of suitable design of the customer application that no injury or damage is caused to third parties in the event of malfunction or failure of an electronic component. Therefore, customer is cautioned to verify that data sheets are current before placing orders. The current data sheets can be downloaded at www.we-online.com.

#### 3. Best Care and Attention

Any product-specific notes, cautions and warnings must be strictly observed. Any disregard will result in the loss of warranty.

#### 4. Customer Support for Product Specifications

Some products within the product range may contain substances which are subject to restrictions in certain jurisdictions in order to serve specific technical requirements. Necessary information is available on request. In this case the field sales engineer or the internal sales person in charge should be contacted who will be happy to support in this matter.

#### 5. Product R&D

Due to constant product improvement product specifications may change from time to time. As a standard reporting procedure of the Product Change Notification (PCN) according to the JEDEC-Standard inform about minor and major changes. In case of further queries regarding the PCN, the field sales engineer or the internal sales person in charge should be contacted. The basic responsibility of the customer as per Section 1 and 2 remains unaffected.

## 6. Product Life Cycle

Due to technical progress and economical evaluation we also reserve the right to discontinue production and delivery of products. As a standard reporting procedure of the Product Termination Notification (PTN) according to the JEDEC-Standard we will inform at an early stage about inevitable product discontinuance. According to this we cannot guarantee that all products within our product range will always be available. Therefore it needs to be verified with the field sales engineer or the internal sales person in charge about the current product availability expectancy before or when the product for application design-in disposal is considered. The approach named above does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.

## 7. Property Rights

All the rights for contractual products produced by Würth Elektronik eiSos GmbH & Co. KG on the basis of ideas, development contracts as well as models or templates that are subject to copyright, patent or commercial protection supplied to the customer will remain with Würth Elektronik eiSos GmbH & Co. KG does not warrant or represent that any license, either expressed or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, application, or process in which Würth Elektronik eiSos GmbH & Co. KG components or services are used.

#### 8. General Terms and Conditions

Unless otherwise agreed in individual contracts, all orders are subject to the current version of the "General Terms and Conditions of Würth Elektronik eiSos Group", last version available at www.we-online.com.

