

KAS500A1/4

✕ OBSOLETE

Alcoswitch

TE Internal #: 2-1437621-7

TE Internal Description: KAS500A1/4=KNOB ALUM 1/4 SHAFT

[View on TE.com >](#)



Switches > Switch Knobs



Primary Product Material: **Aluminum**

Knob Design: **6 Flute**

Shaft Size: **6.35 mm [.25 in]**

Product Diameter: **12.7 mm [.5 in]**

Primary Product Color: **Natural**

Features

Configuration Features

Spinner	Without
Skirt	With
Spin Plate	Without
Knob Design	6 Flute

Body Features

Primary Product Material	Aluminum
Primary Product Color	Natural

Dimensions

Shaft Size	6.35 mm[.25 in]
Product Diameter	12.7 mm[.5 in]

Identification Marking

Indicator Style	Line
Indicator Location	On Skirt

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Yet Reviewed
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold




EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUN 2016 (169) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.


Customers Also Bought




TE Part #2308107-7
DDR4 DIMM 288 PIN TH TYPE




TE Part #321632
TERMINAL,SOLIS HK 12-10 1/4




TE Part #8-1437624-1
PKJT70B1/4=KNOB PLASTIC




TE Part #1-6609941-4
PM00SDHXB=C3428




TE Part #2337230-3
TACT ULTRA TB 3.0X2.0X0.6 240GF



TE Part #1622703-1
LR2 1% 1K3



TE Part #2-1625875-7
CBT 1/4 5% 33K



TE Part #51565-2
SUB MIN SOCKET



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-1437621-7_99_c-2-1437621-7-99.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2-1437621-7_99_c-2-1437621-7-99.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-1437621-7_99_c-2-1437621-7-99.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.