



APC Smart-UPS X, Line Interactive, 2200VA, Rack/tower convertible 4U, 208V-230V, 8x C13+2x C19 IEC, Network card, Extended runtime, Short depth

SMX2200HVNC

Overview

Presentation	Intelligent and efficient network power protection from entry level to scalable runtime. Ideal UPS for servers, point-of-sale, routers, switches, hubs and other network devices.
Lead time	Usually in Stock

Main

Product or component type Uninterruptible power supply (UPS)

Batteries & Runtime

Run Time	View Runtime Graph ☐
Battery type	Lead-acid battery
Extended runtime	1
Number of battery filled slots	0
Number of battery free slots	0
Battery recharge time	3 h
Number of battery replacement quantity	1
Battery life	35 year(s)
Battery charger power	233 W rated

General

Provided equipment	CD with software	
	Documentation CD	
	Installation guide	
	Rack mounting support rails	
	Smart UPS signalling RS-232 cable	
	Temperature probe	
	USB cable	
	Web/SNMP management card	
Number of power module	0	
Number of power module filled slots	0	
Number of power module free slots	0	
Redundant	No	

Physical

Number of rack unit 4U

Cable length	2.00 m	
Number of cables	1	
Colour	Black	
Height	43.2 cm	
Width	17.8 cm	
Depth	48.3 cm	
Net weight	38.56 kg	
Mounting location	Front	
Mounting preference	Lower	
Mounting mode	Rack-mounted	
Two post mountable	1	
USB compatible	Yes	
Input		
Main Input Voltage	208 V 230 V	
Other Input Voltage	220 V 240 V	
Input Connection Type	BS1363A British IEC 320 C20 Schuko CEE 7 / EU1-16P	
Input voltage limits	140280 V	
Network frequency	50/60 Hz +/- 3 Hz auto-sensing	
Output		
Main Output Voltage	208 V 230 V	
Other Output Voltage	208 V	
	220 V 240 V	
Detect or constitution		
Rated power in W	1980 W	
rated power in VA	2200 VA	
output connection type	8 IEC 320 C13 2 IEC Jumpers 2 IEC 320 C19	
Harmonic distortion	Less than 5 %	
Maximum configurable power in	2200 VA	
VA Maximum configurable power in	1980 W	
W Transfer time	6 ms typical : 10 ms maximum	
UPS type	Line interactive	
Wave type	Sine wave	
Output frequency	50/60 Hz +/- 3 Hz sync to mains	

Conformance

Product certifications	CE EAC IRAM			
				RCM
				TISI
	VDE			
	UK PSTI			
Standards	EN/IEC 62040-1:2019/A11:2021			
	EN/IEC 62040-2:2006/AC:2006			
	EN/IEC 62040-2:2018			

Environmental

Acoustic level	55 dBA	
Heat dissipation	150 Btu/h	
Operating altitude	010000 ft	
Ambient air temperature for operation	040 °C	
Ambient air temperature for storage	-1545 °C	
Storage altitude	0.000000000015240.000000000 m	
Relative humidity	095 %	
Storage Relative Humidity	095 %	

Communications & Management

control panel	Multifunction LCD status and control console	
Emergency power off	Yes	
Preinstalled device	Network management card 3 with environmental monitoring	
Control panel	LED status display with on line : on battery : replace battery and overload indicators	
Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays	

Surge Protection and Filtering

Surge energy rate	645 J	
Noise suppression	Full time multi-pole noise filtering : 5% IEEE surge let-through : zero clamping response time : meets UL 1449	

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	33 cm
Package 1 Width	63.3 cm
Package 1 Length	58.6 cm
Package 1 Weight	47.63 kg
Pallet unit layers	2
Pallet layers	4

Contractual warranty

Warranty 3 years repair or replace (excluding battery) and 2 years for battery



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

∇ Environmental footprint	
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	3234
Environmental Disclosure	Product Environmental Profile

Use Better

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant with Exemptions
SCIP Number	0637234b-27c7-4e32-ae29-543dd4803a99
REACh Regulation	REACh Declaration
₩ Energy efficiency	
Optimized Energy Efficiency	Energy efficient product

Use Again

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Removable battery	User replaceable
Take-back	Yes