



# PRODUCT DATASHEET

Datasheet creation date: 2025/06/02 8:59 (UTC)

MOTION & CONTROL  
**NSK**



## HR32210J

### Metric Series Tapered Roller Bearings

#### Dimension series

ISO	3DC	ISO355 dimension series approx.	
<b>Boundary Dimensions</b>			
d	50	mm	Bore diameter
D	90	mm	Outside diameter
T	24.75	mm	Total width
B	23	mm	Width of inner ring
C	19	mm	Width of outer ring
Cup r (min.)	1.5	mm	Chamfer dimension of outer ring (Cup)
Cone r (min.)	1.5	mm	Chamfer dimension of inner ring (Cone)

#### Basic Load Ratings

Cr	108000	N	Basic dynamic load rating
C0r	109000	N	Basic static load rating

#### Speeds



Grease	4000	min-1	Grease lubrication
Oil (Oil-bath)	5300	min-1	Oil-bath lubrication

#### Dimensions

a	21	mm	Effective load center
---	----	----	-----------------------

#### Abutment and Fillet Dimensions

da (min.)	61	mm	Diameter of shaft abutment
Db (min.)	86	mm	Diameter of housing abutment
Da (min.)	78	mm	Diameter of housing abutment
Da (max.)	81	mm	Diameter of housing abutment
Sa	3	mm	Minimum width of space required in housing on large side face
Sb	5.5	mm	Minimum width of space required in housing on small side face
db (max.)	57	mm	Diameter of shaft abutment
ra (max.)	1.5	mm	Radius of shaft or housing fillet of inner ring
ra (max.)	1.5	mm	Radius of shaft or housing fillet of outer ring



#### Calculation factors

e	0.42	Constant
Y0	0.79	Axial load Factors



# PRODUCT DATASHEET

Datasheet creation date: 2025/06/02 8:59 (UTC)

MOTION & CONTROL  
**NSK**

Y1

1.4

Axial load Factors

## Mass

Mass approx.	0.642	kg	Mass approx.
--------------	-------	----	--------------