



Equipped with a SATA III 6Gb/s interface and a powerful controller, Transcend's HSD450T Half-Slim SSD delivesr outstanding transfer speeds in a compact form factor. Following the MO-297 standard set by JEDEC, SATA III 6Gb/s half-slim SSD modules undergo extensive reliability testing to ensure the utmost quality and performance. Powered by 64-layer 3D NAND TLC flash memory and built with DRAM cache, the HSD450T offers not only outstanding 4K random read and write performance but unmatched reliability at an attractive price, best suited to read-heavy applications and space-limited mobile devices such as industrial control systems, medical equipment, mobile devices, and POS terminals.

Features

- Support TRIM and NCQ features
- Advanced Global Wear-Leveling and Intelligent Block management for reliability
- Built-in ECC (Error Correction Code) functionality
- Built-with DRAM Cache
- Support Advanced Garbage Collection and Enhanced S.M.A.R.T. function
- Support Security Command
- · Shock and vibration resistant
- RoHS compliant

Ordering Information


32GB	TS32GHSD450T
64GB	TS64GHSD450T
128GB	TS128GHSD450T



Specifications

Appearance	Dimensions (Max.)	54 mm x 39.8 mm x 4 mm (2.13" x 1.57" x 0.15")	
	Weight (Max.)	8 g (0.28 oz)	
	mSATA Type	MO-297	
	Pin	7+15 pin	
	Form Factor	Half-slim	
Interface	Bus Interface	SATA III 6Gb/s	
Storage	Flash Type	3D TLC NAND flash	
	Capacity	32 GB/64 GB/128 GB	
Operating Environment	Operating Voltage	5V±5%	
	Operating Temperature	0°C (32°F) ~ 70°C (158°F)	
	Storage Temperature	-40°C (-40°F) ~ 85°C (185°F)	
	Humidity	0% ~ 95%	
	Shock	1500 G, 0.5 ms, 3 axis	
	Vibration (Operating)	3 G (peak-to-peak), 5 Hz ~ 800 Hz (frequency)	
	Vibration (Non-operating)	5 G (peak-to-peak), 5 Hz ~ 800 Hz (frequency)	
Power	Power Consumption (Operation)	2.15 watt(s)	
	Power Consumption (Sleep)	0.62 watt(s)	
Performance	Sequential Read/Write (ATTO, max.)	Read: 550 MB/s; write: 400 MB/s	
	Sequential Read/Write (CrystalDiskMark, max.)	Read: 550 MB/s; write: 400 MB/s	
	4K Random Read/Write (IOmeter, max.)	Read: 55,000 IOPS; write: 70,000 IOPS	
	Mean Time Between Failures (MTBF)	1,500,000 hour(s)	
	Terabytes Written (Max.)	80 TB	
	Drive Writes Per Day (DWPD)	0.58 (3 yrs)	
Warranty	Certificate	CE/FCC/BSMI	
	Warranty	Three-year Limited Warranty	
Note	 Speed may vary due to host hardware, software, usage, and storage capacity. The workload used to rate DWPD may be different from your actual workload, which may vary due to host hardware, software, usage, and storage capacity. 		
	<u> </u>		

Mechanical Dimensions



Product specifications are subject to change without notice. Pictures shown may differ from actual products. Total accessible capacity varies depending on operating environment.

Due to the complexity and variety of industrial applications, Transcend cannot guarantee 100% compatibility with all platforms and under all scenarios. For special applications and environments, it is strongly suggested that you contact Transcend beforehand for clarification.



Transcend®