

**Warning:**

6 mm slimBits only to be used in the slimVario bit holder and slimTorque VDE bit holder (VDE torque system).

**SoftFinish® electric slimVario. slimBits.**

1000 V  
IEC 60900:2012

**2831-00** SoftFinish® electric slimVario bit holder with handle and ClicFix, 6.0 mm.

Blade: Chrome-vanadium steel, through-hardened.

Insulation moulded directly onto blade.

Handle: Wiha SoftFinish® electric multi-component handle with roll-off protection.

Bit holder: Insulated metal ClicFix bit holder locks all slimBits reliability.

Only for 6 mm slimBits.

Application: Compact screwdriver together with slimBits.

Attention: Not for use with bit styles C 6.3 and E 6.3.

Order-No.	⊖	↔	⊙	⊙	max. Nm	⊙
34577	6	30	50	160	13	5



1000 V  
IEC 60900:2012

**2831-10** SoftFinish® electric slimBit, slotted.

Individually tested protective insulation 1,000 V AC, VDE and GS tested.

Standards: Manufactured acc. to IEC 60900:2012.

Material: High-quality chrome vanadium steel, through-hardened, bronzed.

Protective insulation moulded directly onto the bit and completely integrated into the blade in the lower area from size 4.0.

Application: For all work on or around electrical components up to 1,000 V AC.

Extra: The integrated protective insulation enables low-lying fastening and spring elements to be reached and manipulated. The slim form of the bit allows easy reaching of the screws below the finger and hand guards.

Attention: 6 mm slimBits only to be used in the slimVario bit holder and slimTorque VDE bit holder (VDE torque system).

Order-No.	⊖	↔	⊙	⊙	max. Nm	⊙
34578	2.5	75	0.4	6.0	0.4	no slim version
34579	3.0	75	0.5	6.0	0.6	no slim version
34580	4.0	75	0.8	6.0	2.5	1
34581	5.5	75	1.0	6.0	5.5	1
34582	6.5	75	1.2	6.0	5.5	1



1000 V  
IEC 60900:2012

**2831-11** SoftFinish® electric slimBit, Phillips.

Individually tested protective insulation 1,000 V AC, VDE and GS tested.

Order-No.	⊕	↔	⊙	max. Nm	⊙
34583	PH1	75	6.0	3.8	1
34584	PH2	75	6.0	5.5	1



1000 V  
IEC 60900:2012

**2831-12** SoftFinish® electric slimBit, Pozidriv.

Individually tested protective insulation 1,000 V AC, VDE and GS tested.

Order-No.	⊕	↔	⊙	max. Nm	⊙
34585	PZ1	75	6.0	3.8	1
34586	PZ2	75	6.0	5.5	1

**slimBits.**

1000 V  
IEC 60900:2012

**2831-13** SoftFinish® electric slimBit, Xeno, for terminal screws (slotted/ Phillips). Individually tested protective insulation 1,000 V AC, VDE and GS tested.

Order-No.	⊕	↔	⊙	max. Nm	⊙
34587	SL/PH1	75	6.0	3.8	1
34588	SL/PH2	75	6.0	5.5	1



1000 V  
IEC 60900:2012

**2831-14** SoftFinish® electric slimBit, Xeno, for terminal screws (slotted/Pozidriv).

Individually tested protective insulation 1,000 V AC, VDE and GS tested.

Order-No.	⊕	↔	⊙	max. Nm	⊙
34589	SL/PZ1	75	6.0	3.8	1
34590	SL/PZ2	75	6.0	5.5	1



1000 V  
IEC 60900:2012

**2831-15** SoftFinish® electric slimBit, TORX®.

Individually tested protective insulation 1,000 V AC, VDE and GS tested.

Order-No.	⊕	↔	⊙	max. Nm	⊙
35506	T8	75	6.0	1.3	no slim version
35507	T10	75	6.0	3.8	no slim version
35508	T15	75	6.0	5.0	1
35509	T20	75	6.0	5.5	1
36071	T25	75	6.0	5.5	1



1000 V  
IEC 60900:2012

**2831-18** SoftFinish® electric slimBit, hexagon.

Individually tested protective insulation 1,000 V AC, VDE and GS tested.

Standards: High-quality chrome vanadium steel, through-hardened, bronzed. Protective insulation moulded directly onto the bit and completely integrated into the blade in the lower area from size 2.5.

Order-No.	⊙	↔	⊙	max. Nm	⊙
37222	1.5	75	6.0	0.9	no slim version
37223	2	75	6.0	1.8	no slim version
37224	2.5	75	6.0	3.8	1
37147	3	75	6.0	5.5	1
37225	4	75	6.0	5.5	1
37226	5	75	6.0	5.5	1
37227	6	75	6.0	5.5	1



1000 V  
IEC 60900:2012

**2831-17** SoftFinish® electric slimBit, square (Robertson).

Individually tested protective insulation 1,000 V AC, VDE and GS tested.

Order-No.	⊙	↔	⊙	max. Nm	⊙
35510	Robertson 1	2.3	75	6.0	5.5
35511	Robertson 2	2.8	75	6.0	5.5