

Power Cutter XGT®

CE002G

Model CE002G is an 80Vmax 355mm (14") cordless power cutter powered by two 40Vmax XGT® Li-Ion batteries in series

This is a dry cutting model and designed to allow for use with vacuum cleaner. This product allows for operation in situations where use of water supply kit should be avoided, such as indoor renovation, modification and more.



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	2 x 40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Brushless Motor	✓
No load speed	4200 min ⁻¹
Max. Depth of Cut	127 mm
Bore Size (Arbor Diameter)	20 / 25,4 mm
Disc Diameter	355 mm
Electronic brake	✓
AWS ready	✓
Vibration Level, Concrete Cutting	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor), Concrete Cutting	1,5 m/s ²
Sound Power Level (L _{WA})	117 dB(A)
Sound Pressure Level (L _{pA})	106 dB(A)

User benefits

- Auto-start Wireless System (AWS) connects to compatible vacuum cleaners with Bluetooth
- Active Feedback sensing Technology (AFT) stops the engine if the rotation suddenly stops
- Electric brake for maximum productivity and increased operator safety
- Battery protection system automatically shuts off power when the battery level is low
- Single LED job light illuminates the work area

Link to product - www.makitauk.com



Related products

Other

User manual

Parts drawing