

CBR-SMD RF COG, Ceramic, 100 pF, 5%, 250 VDC, COG, SMD, Fixed, RF, Ultra High Q, Low ESR, Class I, 0805



Dimensions

| | |
|----------|-----------------|
| L | 2mm +/-0.2mm |
| W | 1.25mm +/-0.2mm |
| T | 0.85mm +/-0.1mm |
| B | 0.5mm +/-0.2mm |

Packaging Specifications

| | |
|----------------------------|--------------------------|
| Packaging: | T&R, 180mm, Plastic Tape |
| Packaging Quantity: | 4000 |

General Information

| | |
|-----------------------|--|
| Supplier: | KEMET |
| Series: | CBR-SMD RF COG |
| Style: | SMD Chip |
| Description: | SMD, Fixed, RF, Ultra High Q, Low ESR, Class I |
| Features: | Ultra High Q, Low ESR, Class I |
| RoHS: | Yes |
| Termination: | Tin |
| Marking: | No |
| Miscellaneous: | Minimum Q = 1400 |
| Notes: | Solder Wave or Solder Reflow |
| Chip Size: | 0805 |

Specifications

| | |
|---|---------------------|
| Capacitance: | 100 pF |
| Capacitance Tolerance: | 5% |
| Voltage DC: | 250 VDC |
| Dielectric Withstanding Voltage: | 500 VDC |
| Temperature Range: | -55/+125C |
| Temperature Coefficient: | COG |
| Dissipation Factor: | 0.10% |
| Aging Rate: | 0% Loss/Decade Hour |
| Insulation Resistance: | 10 GOhms |
| Quality Factor: | 1400 |