




BENEFITS :

- Robust and aesthetic product with its fully painted finish
- Fast, simple, tool-free assembly
- Up to 3 meter high and 1500 kg per bay
- Choice between natural or white hardboard cover or steel sheet shelves
- Kits height 2000 and length 1000, 1250, or 1500 mm available in 5 or 7 levels
- Standard colours : Uprights anthracite grey RAL 7024  Shelves light grey RAL 7035 
- Other colours available on request, high strength Epoxy paint
- For semi-heavy loads, refer to the 'Fliplus' product sheet



Product video

UPRIGHTS TECHNICAL CHARACTERISTICS:

- 1 Perforation every 62,5 mm
- 2 Perforation every 31,25 mm
- « C » Profile 40 x 20 x 10 x 1,5 mm
- Height 1000 to 3000 mm, per increment of 250 mm
- Plastic feet, or galvanized footplates 80x50x3 mm
- Reinforcement crossbraces from 300 to 1200 mm
- Set of 2 bolts 12x60 mm for back-to-back, as an option



SHELVES CHARACTERISTICS:

- One-piece welded tubular shelf, with 4 connectors
- One-piece welded steel sheet shelf, with 4 connectors



Tubular: for the storage of conditioned loads



Steel sheet: for bulk loads or small packaging

SPECIAL SHELVES:




Clothes hanger shelf
1 tube



Clothes hanger shelf
2 tubes



Clothes hanger bar
750 to 1500 mm



Cardboard box special
8 tubes, up to 120 kg

SHELF COVERS:



Natural harboard cover



White cover hardboard



Mesh cover

AVAILABLE ON CONSULTATION:



Galvanized steel sheet cover



Painted steel sheet cover
RAL 7035



Hardboard cover
compatible with central
back panel

Shelf spacing, kits 5 and 7 levels, height 2000 mm
Useful length: 710, 960, 1210, 1460 mm
Center-to-center length: 750, 1000, 1250, 1500 mm
Overall lengths: 790, 1040, 1290, 1540 mm



PRODUCT SHEET

FLIP

BACK PANEL



For a back closure
Length 1000, 1250, 1500 mm
Height 2000 to 3000 mm



White lacquered central
background to separate the 2
sides - same dimensions

FIXING FOR BACK PANEL




8 fixings
1 set per bay

RETAINERS FOR CENTRAL BACK PANEL



Designed to maintain the central back
panel of shelves with no central tube
Compatible with tubular shelves depth
500, 600 and 700 mm

DIVIDERS



To place on shelves
Moving at will
For tubular shelves, natural
hardboard or steel sheet shelves
Height 150 to 300 mm
Depth 300, 366, 400 mm

STOPS FOR TUBULAR SHELVES



Back stop: length 1000,
1250, 1500 mm
Height 50 mm
Fixed to the back tube



Side stop: depth 300 to
700 mm
Metal rod diameter 4 mm
Sendimir finish



Central stop: length
1000, 1250, 1500 mm
Height 50 mm

EXAMPLE LAYOUT



OTHER OPTIONS:

- Plinth RAL 7035, height 100 mm, length 1000, 1250, 1500 mm
- Galvanized gangway sign height 82 x length 122 mm
- Row spacer between uprights to create constant distances and circulating alleys - tubes 20x20 mm, length 300 to 1200 mm, every 100 mm - bolts supplied

YOUR DISTRIBUTOR: