



Main

| | |
|--------------------------------|------------------|
| Range of product | Canalis |
| Product name | KS |
| Product or component type | Feed unit |
| BAR MATERIAL | Aluminium |
| Product compatibility | FL21 gland plate |
| [Ie] rated operational current | 800 A 1000 A |
| Mounting location | Central |
| Colour | White (RAL 9001) |

Complementary

| | |
|--------------------------------|---|
| Protection type | Without protection |
| [Ue] rated operational voltage | 230...690 V |
| Connections - terminals | Lug for 240 mm ² flexible Lug for 300 mm ² rigid |
| Control type | Without |
| Number of circuits | 1 |
| Provided equipment | End cover |
| Mounting mode | By screws |
| Mounting support | Busbar |
| Standards | IEC 61439-6 IEC 60439-2 |
| Width | 1101 mm |
| Depth | 411 mm |
| Height | 606 mm |
| Body material | Metal |
| Net weight | 41.5 kg |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

| | |
|-------------------------|------------------------------|
| IP degree of protection | IP55 conforming to IEC 60529 |
| IK degree of protection | IK08 conforming to IEC 62262 |

Offer Sustainability

| | |
|-----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Halogen content performance | Halogen free product |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

