

5-6450832-9  ACTIVE

TE Internal #: 5-6450832-9

PCB Mount Header, Right Angle, Board-to-Board, 75 Position, 2.54 mm / 6.35 mm [.1 in / .25 in] Centerline, Fully Shrouded, Gold (Au)

[View on TE.com >](#)



Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Type: **PCB Mount Header**

Connector System: **Board-to-Board**

Number of Positions: **75**

Number of Rows: **4**

Centerline (Pitch): **2.54 mm, 6.35 mm [.1 in, .25 in]**

Features

Product Type Features

Mixed & Hybrid Header	Yes
Connector Shape	Rectangular
PCB Connector Type	PCB Mount Header
Connector System	Board-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Connector Product Type	Connector Assembly

Configuration Features

Number of Columns	27
Number of Loaded Positions	50
Number of Positions	75
Number of Rows	4
PCB Mount Orientation	Right Angle
Number of Power Positions	11

Number of Signal Positions	64
----------------------------	----

Electrical Characteristics

Operating Voltage	60 VDC, 200 VDC
-------------------	-----------------

Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

Contact Underplating Material	Nickel
Contact Underplating Material Thickness	1.27 µm[50 µin]
Contact Size	.64mm
Mating Square Post Dimension	.64 mm[.025 in]
PCB Contact Termination Area Plating Material Thickness	2.54 – 5.08 µm[100 – 200 µin]
Contact Shape & Form	Square
Contact Layout	Matrix
Contact Base Material	Copper Alloy
Contact Mating Area Plating Material	Gold (Au)
Contact Type	Blade, Tab
Contact Current Rating (Max)	50 A
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material Thickness	.076 µm[3 µin]

Termination Features

Termination Post & Tail Length	3.43 mm[.135 in]
Square Termination Post & Tail Dimension	.64 mm[.025 in]
Termination Method to PCB	Through Hole - Solder

Mechanical Attachment

Mating Retention	Without
PCB Mount Retention Type	Hold-Down
PCB Mount Alignment Type	Hold-Down
Mating Alignment Type	Polarization
Connector Mounting Type	Board Mount
Mating Alignment	With
PCB Mount Alignment	With
PCB Mount Retention	With

Housing Features

Centerline (Pitch)	2.54 mm, 6.35 mm [.1 in] [.25 in]
Housing Material	High Temperature Thermoplastic Glass-Filled

Dimensions

Connector Width	23.62 mm [.93 in]
Connector Height	14.58 mm [.574 in]
Connector Length	117.86 mm [4.64 in]
Row-to-Row Spacing	2.54 mm [.1 in]
PCB Thickness (Recommended)	2.11 – 2.62 mm [.083 – .103 in]

Usage Conditions

Operating Temperature (Max)	125 °C [257 °F]
Operating Temperature Range	-40 – 125 °C [-40 – 257 °F]

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

Compatible With Agency/Standards Products	UL
UL Rating	Recognized
Glow Wire Rating	High Temperature Part - Not Glow Wire
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	22
Packaging Method	Tray

Other

Position Locations Omitted	P1, P2, P4, P6, P7, Column 1, 12, 13, 14, 15
Number of Blocked Positions	25

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JAN 2025

(247)

Candidate List Declared Against: JAN 2025

(247)

Does not contain REACH SVHC

Halogen Content

Not Low Halogen - contains Br or Cl > 900 ppm.


Solder Process Capability

Wave solder capable to 265°C

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 6450830-1
MBXL R/A HDR 2LP + 8S + 2LP

Customers Also Bought



TE Part #170262-1
EIS CONTACT




TE Part #171631-1
E-J MK-2 070 TAB CONT



TE Part #175289-3
DYNAMIC D-3 TAB CONT. L AU 0.76 L /P



TE Part #179228-6
CRIMP TYPE II RECPT HSG

TE Part #1375819-1
CST-100 II CONTACT TIN PLTTE Part #1971153-2
CONN ASSY INDUSTRIAL MINI I/O J-CONN.TE Part #6450852-7
V/R, ASSY, SOLDER, 5P + 2HDP + 4P + 64S

Documents

Product Drawings

MBXLE R/A HEADER 5P+2HDP+4P+64S

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_5-6450832-9_2.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5-6450832-9_2.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5-6450832-9_2.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English